

NOTES:

1. MATERIALS AND FINISHES:

TNC BULKHEAD JACK, IP 67 COMPLIANT - P/N: 122529-10
MICRO COAX PLUG TERMINATED USING 1.32 MM CABLE - P/N: 100910-01

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM, NOMINAL



3. PACKAGING:

A. QUANTITY: SINGLE PACK
B. BAG TO BE MARKED: AMPHENOL RF, 336209-13-XXXX, AND DATE CODE

336209-13-XXXX

REVISIONS

DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	23-Sep-10	--	KR
	B	SEE SHEET 1	25-Oct-10	2113	KR
	C	SEE SHEET 1	05-Jul-11	2193	HR
	D	SEE SHEET 1	17-Jan-12	2270	CL
	F	SEE SHEET 1	27-Mar-14	2716	MB/BCG



ORDERING INFORMATION	
PART NUMBER (METRIC)	LENGTH IN INCHES * [METERS]
336209-13-0050	1.97 [0.050]
336209-13-0075	2.95 [0.075]
336209-13-0100	3.94 [0.100]
336209-13-0150	5.91 [0.150]
336209-13-0200	7.87 [0.200]
336209-13-0250	9.84 [0.250]
336209-13-0300	11.81 [0.300]

* ADDITIONAL LENGTHS CAN BE PROVIDED, CONTACT AMPHENOL RF MARKETING FOR QUOTE

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:

- ☒ FREQUENCY: DC TO 6.0 GHz
- ☐ VSWR _____ : 1 MAX
- ☐ INS. LOSS _____ dB MAX
- ☒ CONTINUITY
- ☒ HI-POT :200 VRMS
- ☐ OTHER

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE AS FOLLOWS: 2 PLACE DECIMAL ±.015 (0,381 mm) 3 PLACE DECIMAL ±.005 (0,127 mm) ANGLES ± 1°	MATERIAL	DRAWN MOHAN	DATE 18-Mar-14	TITLE TNC BULKHEAD JACK, IP 67 COMPLIANT TO MICRO COAX PLUG TERMINATED, USING 1.32 MM CABLE, VARIOUS LENGTHS		Amphenol Connex		
		SEE NOTES	ENGINEER MOHAN	DATE 18-Mar-14					
		REFERENCE	APPROVED B.C. GLEISSNER	DATE 27-Mar-14					
			CAD FILE			DWG SIZE B	DRAWING NO. 336209-13-XXXX		REV E