

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC		DIST		P		F		ZONE		LTR		F		EC 0720-0279-93		DATE		APPRO	
G	14															6-21-93		BB	

REVISIONS

DESCRIPTION

DATE

APPRO


AMP
WIRE RANGE

3/0 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 2.31±0.08 [0.091±.003]
FOR 17.27 [0.680] MAX WIRE INS DIA



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C

VOLTAGE RATING:

-

CIRCULAR MIL AREA:

76.3-96.3mm² [150,500-190,000]
STRANDED

FINISH

TIN PLATE PER MIL-T-10727

M525036-138
CLASS 2

MILITARY P/N AND CLASS

DO NOT SCALE PRINT.

UNLESS SPECIFIED

DIMENSIONS IN mm [INCHES]

TOLERANCES ON:

2 PLC DEC ± 0.20 [0.008]

3 PLC DEC ± -

ANGLES

MATERIAL

COPPER PER ASTM B-152

NYLON (MIL-M-20693) TYPE 1

COLOR: RED

APPLICATION SPEC

WEIGHT -

LOOSE PC 324185

PACKAGE TYPE

PART NO

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE, TERMINYL
WIRE SIZE: 3/0 AWG

SIZE

CAGE CODE

00779

SCALE

NTS

SHEET

1 OF 1

AMP 1470-15 REV 3-92
23 JUN 1993 14:05:24

AMPT1122 <U0128A>DEPT1132>AMPT1122>U.CUSTOMINYL

CUSTOMER DRAWING