

AC Centrifugal Blowers **Single Inlet, Ø108-120mm**




ebm-papst Mulfingen

- High performance single inlet fans with an external rotor motor offering the advantage of matched motor and impeller in a compact space saving design.
- Motors: IP44 rated, sealed for life, maintenance free, class B insulation and precision ball bearings.
- Impeller: forward curved multi-vane type 'force' fitted for vibration free operation/efficient cooling.
- Scroll: die cast aluminium with motor capacitor, and terminal block May be mounted in any position

Nominal Data			Curve	Voltage	Frequency	Air Flow	Speed/rpm	Power Input	Current Draw	Noise	Perm. Amb. Temp.	Mass
Part Number	Curve	VAC		HZ	M³/h	min ⁻¹	W	A	DB(A)	°C		kg
G2E160-AD03-50	2	230		50	600	2250	240	1.05	72	40		2.9
				60	570	2250	280	1.23	71	40		

AC Centrifugal Blowers Dual Inlet, Ø160mm

Performance Curve



Dimensions

Part Number	H	I	L	O
G2E160-AD03-50	130	100	103	175

