



| Catalogue Number                           | Description                                                                                                                                                         | Carton Quantity |
|--------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|
| <b>POWER PROTECTION RCD SAFETY PLUG</b>    |                                                                                                                                                                     |                 |
| PRCDNB                                     | RCD black safety plug maximum load 3120 watts, 240v AC 30 milli amp trip speed 40 milli seconds (typical) double pole contact break non-latching type               | 10              |
| PRCDB                                      | RCD black safety plug maximum load 3120 watts, 240v AC 30 milli amp trip speed 40 milli seconds (typical) double pole contact break latching type                   | 10              |
| <b>POWER PROTECTION RCD SAFETY ADAPTOR</b> |                                                                                                                                                                     |                 |
| ARCDG                                      | RCD grey safety adaptor maximum load 3120 watts, 240v AC 30 milli amp trip speed 40 milli seconds (typical) double pole contact break, 13 amp fused, latching type  | 10              |
| <b>POWER PROTECTION RCD SAFETY ADAPTOR</b> |                                                                                                                                                                     |                 |
| ARCDNG                                     | RCD grey safety adaptor maximum load 3120 watts, 240v AC 30 milli amp trip speed 40 milli seconds (typical) double pole contact break, non fused, non latching type | 10              |