


IN421
Contractor® Flashlight**Features**

Swivel Head Rotates 180°
Belt Clip
Trigger Switch
Soft Ergonomic Grip
Krypton Bulb

Typical Battery Service

350 mA Continuous
at 21°C (70°F)

**Specifications**

Designation: Energizer Flashlight

Power Source: Four AA Size Batteries (ANSI/NEDA 15 Series)


Configuration: Series - Parallel Circuit

Lamp: No. KPR-102
(Rated at 2.4V, 0.7A)

Lamp Life: Rated at 15 Hours

Lamp Output: Rated at 16.5 Lumens

Typical Weight: 181 grams (6.4 oz.) (without batteries)

Physical Dimensions**Typical Battery Service to 0.9V (per battery) at 21°C (70°F)**

<u>Schedule</u>	<u>Battery Type</u>	<u>Hours (ON Time)</u>
350 mA Continuous	1215	1.0
350 mA Continuous	E91	5.0

Important Notice

This datasheet contains information specific to flashlights manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright Eveready Battery Co. Inc. - All Rights Reserved