

RS Combined Keypad/Proximity

- Vandal resistant
- Die-cast metal
- Operating voltage: 12Vdc
- Programmable 4 Digit code
- Frequency: EM 125Khz
- Read range 5cm
(In noise-free environment)
- 12 Digit keypad (0-9,*,#)
- Output: 1 Relay COM / NO / NC
- 1000+1 Proximity cards, tokens and PIN's
- Strike time: 1 to 99 seconds
- Operating temperature -20°C to 70°C
- 2 LED indicators | green | red

DIMENSIONS	HEIGHT	WIDTH	DEPTH
	120	76	21



All dimensions in mm

