









RECOMMENDED PCB LAYOUT
COMPONENT SIDE
TOLERANCES ARE NON-CUMULATIVE



RECOMMENDED PANEL MOUNT OPENING
MAX. PANEL THK .093/2.362



ASSEMBLED VIEW
SCALE 1:1



NOTES:

1. MATERIALS:

HOUSING: POLYESTER (PBT), GLASS FILLED, UL94 V-0, COLOR: BLACK
TERMINALS: COPPER ALLOY

2. TERMINAL FINISH: 100µN TIN OVER 50µN NICKEL

3. PRODUCT SPECIFICATION: PS-19432-001

4. PACKAGING SPECIFICATION: PK-19437-001

5. MATES WITH: 19432 SERIES RECEPTACLE ASSEMBLIES.

6. RECOMMENDED MOUNTING HARDWARE: (2) #10 X .62/15.7 LONG PLASTIC
THREAD CUTTING SCREWS. RECOMMENDED TORQUE 15-17 IN-LBS.
SUGGESTED SOURCE: ITW SHAKEPROOF INDUSTRIAL BOSSCREW OR EQUIVALENT.

⑦ 7. ALL MATERIALS ARE ROHS COMPLIANT.

REVISE MATERIAL NO. EC NO: WNA2010-0364 DRW: WLEUNG 2009/12/08 CHK: D011TUS 2009/10/16 APPR: D11TUS 2010/05/10 2	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY	DATE	TITLE MX150L RA HDR ASSY 4 WAY, 12-10-8AWG WITH PANEL GASKET  MOLEX INCORPORATED			
			4 PLACES	± ---	± ---	CHECKED BY	DATE				
			3 PLACES	± ---	± .010	DTITUS	2009/10/16				
			2 PLACES	± 0.26	± .02	APPROVED BY	DATE				
			1 PLACE	± 0.5	± ---	DTITUS	2009/10/27				
			ANGULAR ± 3 °			MATERIAL NO. 194370029		DOCUMENT NO. SD-19437-020		SHEET NO. 1 OF 1	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19437-0029](#)