

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
©2006, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	24	Vdc
OPERATING VOLTAGE RANGE	9 ~ 28	Vdc
RATED CURRENT (MAX)	6	mA
INGRESS PROTECTION	IP42	—
COLOR	RED	—
OPERATING TEMPERATURE	-10 ~ +55	°C
HOUSING MATERIAL	ABS	—
TERMINAL MATERIAL	SCREW	—
WEIGHT	100	grams
FLASH RATE	0.5/1	Hz





DETAIL "A"

CONNECTION DETAILS
SWITCH 1 (POWER)

OPEN-LOW (3mA nom)
CLOSED-HIGH (5mA nom)

SWITCH 2 (RATE)
OPEN-SLOW (1/2Hz)
CLOSED-FAST (1Hz)

ON CIT



REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	9/7/06	
A	ADDED BASE NOTE NEW DIMENSION	5/21/07	R.W.
B	REVISED DETAIL "A" DIL SWITCH	3/11/09	B.R.

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.
4. MOUNTS TO AW-05MR OR AW-05MW-NC.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS. TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.

APPROVALS
DRAWN J.D. 9/06

CHECKED R.W. 9/06
APPROVED B.R. 9/06

DO NOT SCALE DRAWING



Doyon, Ohio

SIREN

SIZE A
DRAWING NO. VW-05MR-RL

SCALE: N.T.S.

SHEET 1 OF 1

FILE NAME

VW-05MR-RL.DWG