




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		E1	REVISED PER ECO-11-004835	11MAR11	RK	HMR

D




TERMINATED VIEW

C



A




1 MOLDED PARTS: UL RATED 94V-0 THERMOPLASTIC, BLACK.


2 CONTACTS: PHOSPHOR BRONZE PER QQ-B-750.

3 CONTACTS: PLATED WITH .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000030 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMENATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.


4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.



DETAIL Z
SCALE 10:1
TYPICAL



OBSOLETE	3.100	3.380	3.150	63	64	1-1658623-2
OBSOLETE	2.900	3.180	2.950	59	60	1-1658623-1
	2.400	2.680	2.450	49	50	1-1658623-0
	1.900	2.180	1.950	39	40	1658623-9
	1.600	1.880	1.650	33	34	1658623-8
	1.400	1.680	1.450	29	30	1658623-7
	1.200	1.480	1.250	25	26	1658623-6
	1.100	1.380	1.150	23	24	1658623-5
	.900	1.180	.950	19	20	1658623-4
	.700	.980	.750	15	16	1658623-3
	.600	.880	.650	13	14	1658623-2
	.400	.680	.450	9	10	1658623-1
	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SAMICK 25AUG03	 TE Connectivity					
DIMENSIONS: INCHES		CHK C. ROHDE 25AUG03						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 5°	APVD M. WALMSLEY 25AUG03	NAME RECEPTACLE ASSY, MILITARY POLARIZATION, LEAD FREE, AMP-LATCH™ NOVO					
		PRODUCT SPEC 108-40000						
		APPLICATION SPEC 114-40005	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		MATERIAL	FINISH	WEIGHT	A2	00779	C-1658623	-
		SEE NOTES	SEE NOTES	CUSTOMER DRAWING	SCALE	4:1	SHEET	1 of 1