

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes


Wire Sizes	From	To
Wire Types	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Lengths	1.0 in.	1-5/16 in.
Panduit Color Code on Barrels	GRAY	BLUE
Panduit Die Index No. on Barrels	P29	P24
Alternate Industry Die Index No. ( ) on Barrels	(8)	(7)



CERTIFIED

LISTED

Wire Connector



02	2/04	JHNU CSH	Removed dimension; added note.	11572	PANDUIT CORP. TINLEY PARK, ILLINOIS
REV	DATE	BY	CHK	DESCRIPTION	ECN SCALE N/A DRAWING NO / CAD FILE RSC4-6-CUST