







L712RA
CENTER PIN $\varnothing 0.098$
SCALE 3:1









L722RA
CENTER PIN $\varnothing 0.076$
SCALE 3:1



L732RA
CENTER PIN $\varnothing 0.048$
SCALE 3:1



CIRCUIT DIAGRAM



RECOMMENDED PANEL LAYOUT
(COMPONENT SIDE)

NOTE:
1. FOR HAND INSERTION USE 0.130,
FOR AUTOMATED INSERTION USE 0.135.

2. WASHER AND HEX NUT SHIPPED UNASSEMBLED.

3. MATERIALS:
MOUNTING BUSHING - COPPER ALLOY, NICKEL PLATED
HOUSING - THERMOPLASTIC, BLACK
PIN, SPRING AND TERMINALS - COPPER ALLOY, SILVER PLATED
INSULATORS - PHENOLIC
HARDWARE (NOT SHOWN)
HEX NUT - COPPER ALLOY, NICKEL PLATED
FLAT WASHER - STEEL, NICKEL PLATED

4. THESE PRODUCTS ARE RoHS COMPLIANT.

CUSTOMER DRAWING

						★ STAR SYMBOL DENOTES CRITICAL DIMENSION						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
						UNLESS OTHERWISE SPECIFIED						SIZE	WIDTH	MULT	LBS/M	TEMPER	
						1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ± 0.01 - THREE PLACE DECIMALS ± 0.005 - ANGLES $\pm 1^\circ$ - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.						FINISH	MATERIAL				
						2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ± 0.002						SPEC No.	SCALE				
						3. REMOVE ALL BURRS						FIRST USED ON	3:1				
												DATE DRAWN	BY	CHKD	APVD	Switchcraft®	
												4-MAR-99	MM	3-4-99	JF		
												NAME	LONG BUSHING, RIGHT ANGLE POWER JACK				
												REV	PART No.				
													L7__RA__SERIES				
													SHEET				
													OF				
													I				
													I				
													REV				
													C				