




Aven Tronex Series High Precision Pliers and Cutters

made in the USA

Cutting Edge Technology provides you with superior levels of cutting performance, quality, value and comfort.

- **Highest quality American made** 1% carbon alloy steel is used for exceptional hardness and toughness. Tools are engineered for precision cutting yet long lasting ruggedness. These tools have the heft and feel that of a luxury car.
- **Special Handles** both standard and long are ergonomically designed to fit most hands with no points of pressure. They are enhanced by soft cushion grips for maximum comfort to reduce cutting fatigue dramatically.
- **Exceptional Cutting Edges.** They are made with by using a proprietary dual sharpening process and then raised to optimum hardness and toughness through a induction heating and tempering process. The result: Sharp, hard and tough cutting edges outcut and outlast all others.
- **Superior Joint System:** Two halves of the tool are joined by a fine thread interlocking screw and nut which mount on precision machined bearing rings. This ensures a tight, perfect alignment with smooth consistent cutting.
- Cutters are available in Semi-Flush, Flush and Razor Flush cutting edges.
- Attractive satin coating protects against corrosion and reduces glare.
- Stainless steel double leaf springs
- ESD Safe cushion grips for exceptional comfort
- Available in Standard and Ergonomic handle lengths. Length of tool with standard handle: 115mm (4-1/2") and with ergonomic handle: 140mm (5-1/2")
- 100% Quality assurance:- Each cutter is checked individually at the factory and are warranted for be free of defects in materials and workmanship for the life of the tool



Standard Handle
115mm (4.5")




Ergonomic Handle
140mm (5.5")



Tronex Series - High Precision Cutters


Tronex Oval Head Cutter



Strong versatile and long lasting, this popular shape can be used for many applications. Designed to be durable through hundreds of cuts.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity*
5111	7111	Semi-Flush	.20 to 1.20mm
5112	7112	Flush	.15 to 1.50mm
5113	7113	Razor Flush™	.10 to 1.00mm


Tronex Oval Head Cutter with Relief



Same features as the oval head cutter but the relief provides extra accessibility.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity*
5121	7121	Semi-Flush	.20 to 1.20mm
5122	7122	Flush	.15 to 1.10mm
5123	7123	Razor Flush™	.10 to 0.90mm


Tronex Large Oval Head Cutter



Popular for wire and cable, extra rugged, 25% larger head than standard oval cutters.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity*
5511	7511	Semi-Flush	.20 to 1.50mm
5512	7512	Flush	.15 to 1.50mm
5513	7513	Razor Flush™	.10 to 1.20mm


Tronex Large Oval Head Cutter with Relief



Same features as the large oval head cutter but the relief provides extra accessibility.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity*
5521	7521	Semi-Flush	.20 to 1.40mm
5522	7522	Flush	.15 to 1.40mm
5523	7523	Razor Flush™	.10 to 1.20mm

Tronex Tapered Head Cutter



A more compact design pointed head for increased operator access, yet covers a wide cutting range and long tool life.


Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity*
5211	7211	Semi-Flush	.20 to 1.10mm
5212	7212	Flush	.15 to 1.10mm
5213	7213	Razor Flush™	.10 to 1.00mm

*Diameter of Soft Copper wire



Tronex Series - High Precision Cutters


Tronex Tapered Head Cutter with Relief



Same features as the tapered head cutter but with a lower profile for better access and extra visibility.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity*
5221	7221	Semi-Flush	.20 to 1.10mm
5222	7222	Flush	.15 to 1.00mm
5223	7223	Razor Flush™	.10 to 0.90mm

Tronex Miniature Oval Head Cutter



SMT Cutter, 30% smaller head than standard oval cutters.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity*
5311	7311	Semi-Flush	.20 to 1.10mm
5312	7312	Flush	.10 to 1.00mm
5313	7313	Razor Flush™	.10 to 0.80mm

Tronex Miniature Tapered Head Cutter

54


Precision
Tools



Miniature Taper Relief cutters are used only for exceptionally fine cutting work. Usually access to the cutting area is difficult, requiring the very low profile of this cutter with full relief.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity*
5421	7421	Semi-Flush	.20 to 1.10mm
5422	7422	Flush	.10 to 1.00mm
5423	7423	Razor Flush™	.10 to 0.80mm


Tronex Tip Cutter High Relief



Tip cutter with a deep relief for an exceptionally low profile. Short sturdy jaw. Razor Flush™ cutting Edges.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity
5049	7049	Razor Flush™	.10 to 0.65mm

Tronex Small Tip Cutter




Most popular tip cutter. Jaw is twice as long as standard cutters. Jaw is slim with a low relieved profile. Razor Flush™ cutting edges.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity
5070	7070	Razor Flush™	.10 to 0.65mm

*Diameter of Soft Copper wire

Tronex Series - High Precision Cutters


Tronex Subminiature Tip Cutter



SMT Cutter. Extraordinarily small. Fine cutting edges and fine tip. Often used under a microscope. Removes individual leads from fine pitch components. Razor Flush™ Cutting Edges.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity
5071	7071	Razor Flush™	.05 to 0.40mm

Tronex Angulated Miniature 50° Cutter



An SMT cutter with a very small cutting head. Used for exceptionally fine cutting. Relieved for maximum accessibility. Flush cutting edges.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity
5075	7075	Flush	.10 to 0.65mm

Tronex Angulated Small 50° Cutter



Most popular angulated cutter. Small cutting head with relief for excellent visibility. Durability combined with fine cutting. Flush cutting edges.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity
5082	7082	Flush	.10 to 0.65mm

Tronex Angulated Large 50° Cutter



Largest cutting head. Robust. Excellent in cutting several leads in a single cut. Relieved for enhanced visibility. Razor Flush™ cutting edges.

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity
5072	7072	Razor Flush™	.10 to 0.65mm

Tronex Heavy Duty Cutter



This cutter, forged of carbon steel, has strength in the head and joint areas needed to cut heavier gauge wire or cable. Cushion grips provide operator comfort. A jaw restraining device is attached to insure spring retention. Overall length 6" (152mm). Length of cutting blade 3/4" (19mm)

Standard Handle	Ergonomic Handle	Cutting Edge	Cutting Capacity
-	7812	Flush	.10 to 1.60mm

*Diameter of Soft Copper wire



Tronex Series - High Precision Pliers

Tronex Chain Nose Pliers: Standard and Short Jaw



Features very fine tips, "eased" edges of the inner jaw to reduce the risk of damage to the workpiece during forming, and a long jaw for extended gripping power. Available with smooth or serrated jaws. Standard & Short Chain nose pliers have tips dimension of 1.2mm W x 1.4mm H (.050" x .060").

Standard Handle	Ergonomic Handle	Jaw Type	Jaw Length
511	711	Standard Smooth	33mm (1.30")
512	712	Standard Serrated	33mm (1.30")
513	713	Short Smooth	19mm (0.75")

Tronex Needle Nose Pliers



These pliers have exceptionally fine tips. The outer surface of the jaw is rounded to the shape of smooth half cones. This design increases tool access and allows forming of round loops. All edges of the inner jaws are eased. Tip dimensions: 1.0mm W x 1.2mm H. (.040" x .050").

Standard Handle	Ergonomic Handle	Jaw Type	Jaw Length
521	721	Smooth	31.7mm (1.25")

Tronex Round Nose Pliers: Standard and Short Jaw



Available in long and short jaws. The long jaws makes it possible to form a wide range of loop diameters. The short jaw adds more stiffness and strength to allow forming of heavier gauge wire with added control. Long jaw pliers have a tip diameter of 0.7mm(.030") and the short jaw pliers have a tip diameter of 0.9mm (.035").

Standard Handle	Ergonomic Handle	Jaw Type	Jaw Length
531	731	Smooth	31.7mm (1.25")
532	732	Smooth	18.1mm (.715")

Tronex Flat Nose Pliers: Standard and Wide Tips



These flat nose pliers have a long jaw and very thin tips. The tip gripping area has a smooth finish. All inner edges are "eased" to reduce risk of workpiece damage. Standard flat nose pliers have tips that are 3.5mm (.140") wide and the Wide Tip Flat Nose Pliers have tips that are 6.3mm (.250") wide.

Standard Handle	Ergonomic Handle	Jaw Type	Jaw Length
541	741	Standard Smooth	31.7mm (1.25")
542	742	Wide Smooth	31.7mm (1.25")