



SCHEMATIC

MATERIALS:

Connector:

Body: Tarnish Resistant Plating, Center Contact: Female - Gold Plated Beryllium Copper, Male – Gold Plated Brass

Solder Turret Terminal Screws: Steel

Shielded Housing: Die cast aluminum alloy A380 and A394

Finish: Blue paint per Federal Standard 595. Color No. 25109

Cover: 1.02 (.040) thick aluminum alloy 1100-H14

Finish: Clear anodized.

Screws: Steel 4 each 2-32 x 6.35 Pan Head, self-tapping.

Finish: Blue Zinc plated.

RATINGS:

Operating Voltage: Inner conductor/Shield: 500 VRMS Max.

Operating Temperature: -55°C to +150°C

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 2391

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[2391](#)