

GWl 10.8v Angle Drill

Cordless screwdriver



The most compact lithium -ion cordless angle driver

Extremely versatile, above all in tight spaces and hard -to -reach areas, thanks to the 5 head position settings: 0°/22.5°/45°/67.5°/90°

Very compact: 9.5 cm adjustable head, the smallest on the market

7 -stage electronic torque adjustment + drill setting

Unique Bosch Premium lithium -ion technology for 400% longer lifetime and unbeatable battery runtime

Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and total discharge

Motor brake for precise work when driving rows of screws

Practical hook for storage and accessibility

Bosch Hyper Charge: due to the rapid charging process, the batteries are charged to 75% after just half of the charge time

No memory effect: the battery can be charged regardless of the charging state at any time, without damaging the cells

Torque, max. (hard screwdriving applications): 13 Nm

Torque, max. (soft screwdriving applications): 5 Nm

No -load speed: 0 - 585 rpm

Battery type: Lithium -ion

Battery voltage: 10,8 V

Battery capacity: 1,3 Ah

Weight incl. battery: 1,1 kg

Charging time, approx.: 30 min

Torque settings: 7+1

Length: 95,0 mm

Height: 295,0 mm

Max. drilling diameter in aluminium: 8 mm

Max. drilling diameter in wood: 10 mm

Max. drilling diameter in steel: 8 mm

Max. screw diameter: 5 mm

Forward/reverse operation

Electronic

Softgrip

INCLUDES

2 X 1.3AH BATTERIES

CHARGER