

**Cable glands
VG 11-K68 SKS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Cable gland with spiral kink protection specially for
flexible connections

General ordering data

Order No.	1720490000
Type	VG 11-K68 SKS
Version	Cable gland, Polyamide 6, RAL 7035, External thread: PG 11
GTIN (EAN)	4008190358709
Qty.	100 pc(s).

Cable glands
VG 11-K68 SKS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	89 mm	Net weight	14.04 g
--------	-------	------------	---------

General information

AF size 1	22 mm	Cable gland	PG
Clamping range, max.	10 mm	Clamping range, min.	5 mm
Colour code	RAL 7035	DIN	EN 50262 (for M thread)
External thread	PG 11	Length of thread	8 mm
Material	Polyamide 6	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Seal insert	CR
Torque for cap nut, max.	3 Nm	Torque for cap nut, min.	2 Nm
Torque for connecting adapter, max.	2.5 Nm	Torque for connecting adapter, min.	1.5 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 2.0	EC000441	ETIM 3.0	EC000441
UNSPSC	30-21-18-01	eClass 4.1	27-14-12-09
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Approvals

Approvals



ROHS	Conform
------	---------