



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: RBC6A

UPS Replacement Battery Cartridge for select APC UPS

Highlights



- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery set is carefully configured to meet or exceed all of the original manufacturer specifications and ships pre-assembled and ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with select UPS systems from APC and other major brands See Tripp Lite's UPS replacement battery page to confirm compatibility and quantity required.

Applications

- Extends the operating life of older UPS systems
- Restores or enhances runtimes of UPS systems exhibiting reduced power failure runtime

Package Includes

- UPS battery replacement cartridge
- Instruction manual with installation, recycling and warranty information

Features

- Restore your UPS to its original runtime specifications
- Comes pre-assembled and ready for installation into your UPS system
- Reusable packaging holds expired batteries for recycling center delivery
- Compatible with many brands and models, including APC models BP1000, SUVS1000, SU1000, SU1000NET, SU1000RM, SU1000RMNET, and SUA1000

Specifications

BATTERY	
Typical battery lifespan	3 - 5 years, depending on host UPS operating conditions
PHYSICAL	
Shipping Dimensions (HWD/in)	6 x 7.5 x 12

Shipping Dimensions (HWD/cm)	15.2 x 19.1 x 30.5
Shipping weight (lbs)	19 (Package includes 1 set of 2 batteries)
Shipping weight (kg)	8.6 (Package includes 1 set of 2 batteries)
Unit Dimensions (HWD/in)	The set measures 3.6875 x 7.6875 x 5.875
Unit Dimensions (HWD/cm)	The set measures 9.4 x 19.5 x 14.9
Unit weight (lbs)	16.9
Unit weight (kg)	7.7
ENVIRONMENTAL	
Relative Humidity	0 - 95% non-condensing
Operating Elevation (ft.)	0 - 10,000
Storage Elevation (ft.)	0 - 50,000
Operating Elevation (m)	0-3000 m
Storage Elevation (m)	0 - 15,200 m
WARRANTY	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2537.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.