




DESCRIPTION: 64 PIN DIN FEMALE DIP SOLDER



689-096-290-001
096 = ROWS A AND C ONLY



Materials:
Insulator: Glass-Filled PBT U.L. rated 94V-0
Contacts: Cu Alloy, Double Spring Hardened

Electricals:
Current Rating: 1 Amp max for 28 AWG , 1.5Amp max. for 26 AWG
Operating Temperature: -40°C to +145°C



THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF NorComp AND
SHALL NOT BE REPRODUCED, COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OF SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN:
WAYNE ROBBINS

DATE:
10-19-98

CHECKED:

DATE:

SCALE:
1:1

SHEET
1 OF 1

REV
1

DWG NO.
689-XXX-290-001