

219XA Series, 5×20mm, Time-Lag Fuse



Agency Approvals

Agency	Agency File Number	Ampere Range
	Cartridge: NBK220604-E10480A NBK120802-E10480C	1A – 5A 6.3A
	Leaded: NBK220604-E10480B NBK120802-E10480D	1A – 5A 6.3A
	2004010207110266 2003010207079982	0.125A – 0.800A 1A – 6.3A
	E10480	0.040A – 6.3A
	29862	0.125A – 6.3A
	1402844	0.040A – 6.3A
	40016080	0.125A – 6.3A
	KM41462	0.125A – 6.3A
	N/A	0.040A – 6.3A

Description

5×20mm time-Lag glass body cartridge fuse designed to IEC specification

Features

- Designed to International (IEC) Standards for use globally
- Meets the IEC 60127-2, Sheet 6 specification for time-Lag fuses
- Available in cartridge and axial lead form
- RoHS compliant and lead-free

Applications

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

Electrical Characteristics for Series

% of Ampere Rating	Ampere Rating	Opening Time
150%	0.04A - 0.1A	1 hours, Minimum
	0.125A – 6.3A	1 hours, Minimum
210%	0.04A - 0.1A	2 minutes, Maximum
	0.125A – 6.3A	2 minutes, Maximum
275%	0.04A - 0.1A	0.2 sec., Min; 10 sec. Max
	0.125A – 6.3A	0.6 sec., Min; 10 sec. Max
400%	0.04A - 0.1A	0.04 sec., Min; 3 sec. Max
	0.125A – 6.3A	.15 sec., Min; 3 sec. Max
1000%	0.04A - 0.1A	.01 sec., Min; 0.3 sec. Max
	0.125A – 6.3A	.02 sec., Min; 0.3 sec. Max

Additional Information



Datasheet



Resources



Samples

Axial Lead & Cartridge Fuses


5x20 mm > Time-Lag > 219XA Series

Electrical Characteristic Specifications by Item

Amp Code	Amp Rating (A)	Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec)	Maximum Voltage Drop at Rated Current (mV)	Maximum Power Dissipation at 1.5I _n (W)	Agency Approvals							
															
.040	0.040	250	150A @ 250VAC	31.8620	0.01640	4000	1.6				x		x		x
.050	0.050	250		21.2920	0.01700	3500	1.6				x		x		x
.063	0.063	250		14.2685	0.03800	3000	1.6				x		x		x
.100	0.100	250		6.0180	0.07900	2500	1.6				x		x		x
.125	0.125	250		4.2000	0.13000	2000	1.6	x			x	x	x	x	x
.160	0.160	250		2.5500	0.31000	1900	1.6	x			x	x	x	x	x
.200	0.200	250		1.6000	0.32000	1500	1.6	x			x	x	x	x	x
.250	0.250	250		1.0495	0.54000	1300	1.6	x			x	x	x	x	x
.315	0.315	250		0.8475	1.23000	1100	1.6	x			x	x	x	x	x
.400	0.400	250		0.5350	1.40000	1000	1.6	x			x	x	x	x	x
.500	0.500	250		0.3700	3.00000	900	1.6	x			x	x	x	x	x
.630	0.630	250		0.2750	4.82000	300	1.6	x			x	x	x	x	x
.800	0.800	250		0.1635	9.35000	250	1.6	x			x	x	x	x	x
001.	1.00	250		0.1165	19.20000	150	1.6	x	x		x	x	x	x	x
1.25	1.25	250		0.0817	27.15000	150	1.6	x	x		x	x	x	x	x
01.6	1.60	250		0.0551	44.20000	150	1.6	x	x		x	x	x	x	x
002.	2.00	250		0.0452	92.70500	150	1.6	x	x		x	x	x	x	x
02.5	2.50	250		0.0305	138.00000	120	1.6	x	x		x	x	x	x	x
3.15	3.15	250		0.0231	202.00000	100	1.6	x	x		x	x	x	x	x
004.	4.00	250		0.0158	330.00000	100	1.6	x	x		x	x	x	x	x
005.	5.00	250		0.0117	544.00000	100	1.6	x	x		x	x	x	x	x
06.3	6.3	250		0.0107	1093.03500	100	1.6	x	x		x	x	x	x	x


*4A-6.3A have an Interrupting rating 100A@350Vac.

Temperature Re-rating Curve




Note:
Rerating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

Average Time Current Curves



Soldering Parameters - Wave Soldering



Recommended Process Parameters:

Wave Parameter	Lead-Free Recommendation
Preheat: (Depends on Flux Activation Temperature)	(Typical Industry Recommendation)
Temperature Minimum:	100°C
Temperature Maximum:	150°C
Preheat Time:	60-180 seconds
Solder Pot Temperature:	260°C Maximum
Solder Dwell Time:	2-5 seconds

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350°C +/- 5°C
Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

Axial Lead & Cartridge Fuses

5×20 mm > Time-Lag > 219XA Series


Product Characteristics

Materials	Body: Glass Cap: Nickel Plated Brass Leads: Tin Plated Copper
Terminal Strength	MIL-STD-202, Method 211, Test Condition A
Solderability	MIL-STD-202 Method 208
Product Marking	Cap 1: Brand logo, current and voltage rating Cap 2: Agency approval markings Series
Packaging	Available in Bulk (M=1000 pcs/pkg) or on Tape/Reel (MRET1=1000 pcs/reel)


Operating Temperature	–55°C to +125°C
Shock	MIL-STD-202, Method 107, Test Condition B: (5 cycles –65°C to +125°C)
Vibration	MIL-STD-202, Method 201
Humidity	MIL-STD-202, Method 103, Test Condition A high RH (95%) and elevated temperature (40°C) for 240 hours.
Salt Spray	MIL-STD-202 Method 101, Test Condition B

Dimensions

0219 000XAP



0219000XAEP



Notes:

* Ratings above 6.3A have 0.8±0.05 diameter lead.

Part Numbering System

0219 xxxx M XA E P

Series

Amp Code

Refer to Amp Code column of Electrical Characteristics Table

Quantity Code

M = 1000

Packaging Code

X = Filler

A = Enhanced I sq t

Option Codes

Blank : Cartridge Type Fuse

E : Axial Leaded Fuse

Lead-free

Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width
219XA Series				
Bulk	N/A	1000	MXA	N/A
Bulk	N/A	1000	MXAE	N/A
Reel and Tape	EIA 296-E	1000	MRAET1	T1=53mm (2.087")
Bulk	N/A	1000	MXG	N/A