

VG-FPZ Series


for inverter installed home appliances' surge control

[RoHS Compliant]




Model	Rated voltage AC/DC (V)	Rated current AC/DC (A)	Withstanding voltage 1 min., line to ground AC (V)	Insulation resistance 500VDC 1 min., line to ground (MΩ) min.	Leakage current 250V/60Hz, (mA) max.	Operating temperature range (°C)	Weight (g)
VG-2150FPZ-10	100	15	1000	300	0.5 (125V)	-25~+55	200
VG-2150FPZ-20	200	15	1500	300	1.0 (250V)	-25~+55	200
VG-2200FPZ-10	100	20	1000	300	0.5 (125V)	-25~+55	220

Shape and Dimensions




*Faston® is a registered trademark of Tyco Electronics AMP. [mm]

Circuit Diagram



Caution: Ⓔ represents a case.

Attenuation Characteristics



- All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact TOKIN for updated product data.
- Please request for a specification sheet for detailed product data prior to the purchase.
- Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.