

[Add to BOM](#) | [Add to Favorites](#)

4-Way Cable Tie Mounts Without Adhesive

Product Details Related Documents

Std. Pallet Volume (cf)	46.010250
Std. Pallet Weight (lb)	536.4000
Std. Ctn. Volume (cf)	1.2781
Std. Ctn. Weight (lb)	14.9000
Std. Pkg. Qty.	500
RoHS Compliancy Status	Compliant
Part Description	4-Way Cable Tie Mounts Without Adhesive
Product Type	Cable Tie Mounts - User Supplied Adhesive
Material	Nylon 6.6
Color	White
UL Recognized	E136577
Width (In.)	1.00
Length (In.)	1.00
Height (mm)	5.1
Height (In.)	0.20
Width (mm)	25.4
Length (mm)	25.4
CE Compliant	Yes
Flammability Rating	V-2
Screw Size Metric	M3
Screw Size	#6 (M3)
Type	Tie Mount - User Supplied Adhesive
Pricing Description	Cable Tie Mount, #6 Screw (M3), 1"x1" (25.4mm x 25.4mm), WH
Used With Cable Ties	M, I, S
Mounting Method	#6 (M3) Screw or User Supplied Adhesive
Environment	Indoor
Max. Bundle Diameter (mm)	4.8
Min. Order Qty.	500.0000

