


Product Description

Space saving installation due to small cable diameters; High electrical performance due to 4 kV test voltage



Features:

- Flame retardant according to IEC 60332-1-2.
- Good chemical resistance.

Application Range

Plant engineering and construction Industrial machinery Air conditioning installations power station stage technique.
Fixed installation as well as occasional flexing at free, non-continuously recurring movement without tensile load.
Dry or damp interiors under medium mechanical load conditions.

Benefits

Space saving installation due to small cable diameters.
High electrical performance due to 4 kV test voltage.

Design

Fine strands of bare copper wires.
PVC insulation LAPP P8/1.
Cores twisted in layers.
PVC outer sheath, grey (RAL 7001).

Technical Data

Core Identification Code	Black with White Numbers acc. to VDE 0293
Specific Insulation Resistance	> 20 Gohm × cm
Conductor Stranding	Fine wire in Accordance to VDE 0295 class 5 / IEC 60228 class 5
Minimum Bending Radius	Occasional Flexing : 15 × Cable Diameter Fixed Installation : 4 × Cable Diameter
Rated Voltage	U0/U: 300 / 500 V
Test Voltage	4,000 V
Protective Conductor	G = with Protective Conductor Green / Yellow X = without Protective Conductor
Range of Temperature	Occasional Flexing : -5°C up to +70°C Fixed Installation : -40°C up to +80°C
VDE tested	VDE Reg. No. 7030 for Following Sizes: up to 2.5 mm ² : 2-64 Cores Starting at 4 mm ² : 2-7 Cores

Specification Table

Description	Number of Cores and mm ² per Conductor	Outer Diameter mm	Copper Index kg / km	Weight kg / km	Part Number
Cable, YY, 3 Core, 0.75 mm, 50M	3 G 0.75	5.7	21.6	55	PPYY3C0.75 50M
Cable, YY, 3 Core, 1 mm, 50M	3 G 1	6	28.8	65	PPYY3C1.00 50M
Cable, YY, 3 Core, 1.5 mm, 50M	3 G 1.5	6.7	43	84	PPYY3C1.50 50M
Cable, YY, 4 Core, 0.75 mm, 50M	4 G 0.75	6.2	28.8	66	PPYY4C0.75 50M
Cable, YY, 4 Core, 1 mm, 50M	4 G 1	6.5	38.4	79	PPYY4C1.00 50M
Cable, YY, 4 Core, 1.5 mm, 50M	4 G 1.5	7.2	58	104	PPYY4C1.50 50M
Cable, YY, 3 Core, 2.5 mm, 50M	3 G 2.5	8.1	72	132	PPYY3C2.50 50M
Cable, YY, 5 Core, 0.75 mm, 50M	5 G 0.75	6.7	36	79	PPYY5C0.75 50M
Cable, YY, 7 Core, 0.75 mm, 50M	7 G 0.75	7.3	50	101	PPYY7C0.75 50M
Cable, YY, 5 Core, 1 mm, 50M	5 G 1	7.1	48	94	PPYY5C1.00 50M
Cable, YY, 7 Core, 1 mm, 50M	7 G 1	8	67	126	PPYY7C1.00 50M
Cable, YY, 5 Core, 1.5 mm, 50M	5 G 1.5	8.1	72	128	PPYY5C1.50 50M
Cable, YY, 7 Core, 1.5 mm, 50M	7 G 1.5	8.9	101	166	PPYY7C1.50 50M
Cable, YY, 4 Core, 2.5 mm, 50M	4 G 2.5	8.9	96	163	PPYY4C2.50 50M
Cable, YY, 5 Core, 2.5 mm, 50M	5 G 2.5	10	120	200	PPYY5C2.50 50M
Cable, YY, 12 Core, 0.75 mm, 50M	12 G 0.75	9.9	86	171	PPYY12C0.75 50M
Cable, YY, 18 Core, 0.75 mm, 50M	18 G 0.75	11.7	130	244	PPYY18C0.75 50M
Cable, YY, 12 Core, 1.5 mm, 50M	12 G 1.5	12	173	279	PPYY12C1.50 50M
Cable, YY, 18 Core, 1.5 mm, 50M	18 G 1.5	14.4	259	407	PPYY18C1.50 50M
Cable, YY, 7 Core, 2.5 mm, 50M	7 G 2.5	11.1	168	267	PPYY7C2.50 50M
Cable, YY, 3 Core, 0.75 mm, PER M	3 G 0.75	5.7	21.6	55	PPYY3C0.75
Cable, YY, 3 Core, 1 mm, PER M	3 G 1	6	28.8	65	PPYY3C1.00
Cable, YY, 3 Core, 1.5 mm, PER M	3 G 1.5	6.7	43	84	PPYY3C1.50
Cable, YY, 3 Core, 2.5 mm, PER M	3 G 2.5	8.1	72	132	PPYY3C2.50
Cable, YY, 4 Core, 0.75 mm, PER M	4 G 0.75	6.2	28.8	66	PPYY4C0.75
Cable, YY, 4 Core, 1 mm, PER M	4 G 1	6.5	38.4	79	PPYY4C1.00
Cable, YY, 4 Core, 1.5 mm, PER M	4 G 1.5	7.2	58	104	PPYY4C1.50
Cable, YY, 4 Core, 2.5 mm, PER M	4 G 2.5	8.9	96	163	PPYY4C2.50
Cable, YY, 5 Core, 0.75 mm, PER M	5 G 0.75	6.7	36	79	PPYY5C0.75
Cable, YY, 5 Core, 1 mm, PER M	5 G 1	7.1	48	94	PPYY5C1.00
Cable, YY, 5 Core, 1.5 mm, PER M	5 G 1.5	8.1	72	128	PPYY5C1.50
Cable, YY, 5 Core, 2.5 mm, PER M	5 G 2.5	10	120	200	PPYY5C2.50
Cable, YY, 7 Core, 0.75 mm, PER M	7 G 0.75	7.3	50	101	PPYY7C0.75

Specification Table

Description	Number of Cores and mm ² per Conductor	Outer Diameter mm	Copper Index kg / km	Weight kg / km	Part Number
Cable, YY, 7 Core, 1 mm, PER M	7 G 1	8	67	126	PPYY7C1.00
Cable, YY, 7 Core, 1.5 mm, PER M	7 G 1.5	8.9	101	166	PPYY7C1.50
Cable, YY, 7 Core, 2.5 mm, PER M	7 G 2.5	11.1	168	267	PPYY7C2.50
Cable, YY, 12 Core, 0.75 mm, PER M	12 G 0.75	9.9	86	171	PPYY12C0.75
Cable, YY, 12 Core, 1.5 mm, PER M	12 G 1.5	12	173	279	PPYY12C1.50
Cable, YY, 18 Core, 0.75 mm, PER M	18 G 0.75	11.7	130	244	PPYY18C0.75
Cable, YY, 18 Core, 1.5 mm, PER M	18 G 1.5	14.4	259	407	PPYY18C1.50

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2011.