





SECTION A-A  
PARTIAL

1. CONTACTS ARE SHOWN IN POSITION FOR ILLUSTRATION ONLY. FOR SHIPMENT, CONTACTS ARE INCLUDED IN A CONTAINER WITHIN THE CONNECTOR PACKAGE.
2. ALL CONTACT CAVITIES IN MODULES "A" & "B" ARE LOCATED WITHIN .006 DIA. TRUE POSITION. ALL CONTACT CAVITIES IN MODULE "C" ARE LOCATED WITHIN .020 DIA TRUE POSITION.
3. COAX CONTACTS NOT SUPPLIED IN KITS\_\_\_ MUST BE ORDERED SEPARATELY.
4. POLARIZING KEYS SHOWN IN POSITION "01" FOR ILLUSTRATION ONLY— CONNECTORS SHIPPED WITH KEYING PER ORDERING INSTRUCTIONS. CONTACT INSERTS AS SHOWN FOR ILLUSTRATION ONLY— SEE TABLE FOR DESCRIPTIVE NUMBER.

5 INSERT MATERIAL: DIE CAST ALUMINUM PER ASTM-B-85

|                                         |                      |             |
|-----------------------------------------|----------------------|-------------|
| PRELIMINARY NOT RELEASED FOR PRODUCTION | NIC66G23A05SF1       | 2-208970-8  |
| PRELIMINARY NOT RELEASED FOR PRODUCTION | NIC66G23A05AA1       | 2-208970-7  |
| —                                       | NIC66G21A03AA0       | 2-208970-6  |
| (G21A29CC1) w/DUST CAP                  | SPECIAL              | 2-208970-5  |
| —                                       | NIC66G21A05CC0       | 2-208970-4  |
| —                                       | NIC66G21A01CC0       | 2-208970-3  |
| —                                       | NIC66G21A02CC0       | 2-208970-2  |
| C4/150/13C2 WITH CONTACTS & COAX        | SPECIAL              | 2-208970-1  |
| —                                       | ADVANCED PART NUMBER | 2-208970-0  |
| —                                       | SPECIAL              | 1-208970-9  |
| —                                       | NIC66G21A01SC1       | 1-208970-8  |
| —                                       | NIC66G21A19AA0       | 1-208970-7  |
| —                                       | NIC66G26A01AA0       | 1-208970-6  |
| —                                       | NIC66G51A01AA0       | 1-208970-5  |
| —                                       | NIC66G21A00AA0       | 1-208970-4  |
| —                                       | NIC66G21A02AA0       | 1-208970-3  |
| —                                       | NIC66G21A02AA1       | 1-208970-2  |
| —                                       | NIC66G21A01CA0       | 1-208970-1  |
| —                                       | NIC66G21A09CC0       | 1-208970-0  |
| —                                       | —                    | 208970-9    |
| BLANK/150/13C2 WITH CONTACTS            | NIC66G51A01AA0       | 208970-8    |
| —                                       | ADVANCED PART NUMBER | 208970-7    |
| —                                       | NIC66G21A01CC1       | 208970-6    |
| —                                       | NIC66G21A01BA1       | 208970-5    |
| —                                       | NIC66G21A01AA1       | 208970-4    |
| —                                       | NIC66G21A01SB1       | 208970-3    |
| —                                       | NIC66G21A01AC0       | 208970-2    |
| —                                       | NIC66G21A01AA0       | 208970-1    |
| REMARKS                                 | DESCRIPTIVE NUMBER   | PART NUMBER |

|                                                                                       |  |                                                                                                                                              |  |                                                                                                       |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN C.G.THOMAS 4-23-01<br>QIR S.G.LATFELTER 4-23-01<br>APP'D S.G.LATFELTER 4-23-01                                                           |  |  TE Connectivity |  |
| DIMENSIONS:<br>INCHES                                                                 |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 .PLC ± .—<br>1 .PLC ± .—<br>2 .PLC ± .—<br>3 .PLC ± .005<br>4 .PLC ± .—<br>ANGLES ± .—<br>FINISH |  | NAME RECEPTACLE ASSY, SIZE 2, CLASS A, ARINC 600<br>—                                                 |  |
|  |  | PRODUCT SPEC<br>APPLICATION SPEC                                                                                                             |  | SIZE   CASE CODE   DRAWING NO<br>A1   00779   C=208970                                                |  |
| MATERIAL SEE CALLOUTS                                                                 |  | WEIGHT —                                                                                                                                     |  | RESTRICTED TO                                                                                         |  |
| SEE CALLOUTS                                                                          |  | CUSTOMER DRAWING                                                                                                                             |  |                                                                                                       |  |
|                                                                                       |  | SCALE 1:1                                                                                                                                    |  | SHEET 1 OF 1 REV S                                                                                    |  |