

Switchcraft®



MOLDED CABLE ASSEMBLIES 3.5 mm with Plugs

1. 35HRXXX35
2. 36HRXXX36
3. 35HRXXX84

FEATURES AND BENEFITS

- Choose plug-to-plug or plug-to-stripped and tinned leads
- 3.5 mm plugs available as straight or right-angle

- Available in mono and stereo
- NOM. 26 AWG jacketed conductors (red and white) with copper spiral shield
- Cable O.D. 3.0 mm nom./ .118" nom.
- Black cable

ORDERING

1. Order by part number ("XXX" is length in inches).
2. Contact Switchcraft for custom requirements.

PART NUMBERING SYSTEM

				
32 - Mono 33 - RA Mono 35 - Stereo 36 - RA Stereo	H - Black	R - 3.0 mm nom. 2-conductor wire with spiral copper shield	Length (feet) 036 (3) 072 (6) 144 (12)	32 - Mono 33 - RA Mono 35 - Stereo 36 - RA Stereo 84 - Stripped and tinned 90 - Straight Cut Off

SPECIFICATIONS

PLUG

Tip, Ring and Sleeve: Brass with nickel-plate

Flex Life: 5000 cycles minimum

Plug Insulator: ACETAL