



Get Switched On to Outdoor Safety!

WEATHERSAFE
IP66
RATING



SIMPS
Safety Isolator Mains Protection Switch

A tough and durable range of weatherproof switches, sockets and fused connection units for outdoor installations.



OUTDOOR MULTI-CONNECTOR BOX.
See inside for details.



Weathersafe Outdoor Power

What is Timeguard Weathersafe®?

Whenever sockets and switches are installed outside or in public spaces, extra protection is called for

to ensure that the installation is reliable, electrically safe and secure against vandalism and theft.

The Timeguard Weathersafe®

range of switched sockets and fused connection units covers all three areas of concern (patents granted) providing all the reassurance that you need.



Reliable and Durable.

Timeguard Weathersafe® sockets and switches offer IP66 protection against the elements of dust and rain, splashing water, hose directed water and external ice formation, and are therefore more than equal to UK weather conditions!

The tough impact resistant housings with neoprene seals mean that you can expect years of good service from even the toughest environments where the occasional impact is only to be expected.



Safety and Security.

Timeguard insisted that unique safety features were built-in when designing Timeguard Weathersafe®.

The result is a special unique mains isolation switch **SIMPS** which isolates the power supply when the housing is opened.

This option makes Timeguard Weathersafe® the ideal outdoor sockets of choice for use in public buildings and open spaces.



Also, twin gang RCD protected switched socket versions offer additional protection against the dangers of electrocution for use with a whole series of outdoor power equipment, including lawnmowers, hedge trimmers, power washers etc.

To provide additional security, Timeguard's lockable covers keep vandals OUT and also ensure that only authorised persons use the power supply that, in these days of rising fuel prices and levies, is no minor concern! The fixing screws are hidden behind the lockable cover for extra safety and security.





True to form for Timeguard, the range is easy to install, with multiple replaceable knock out cable entries.

Availability and Choice.

See opposite for our complete range of switches, sockets and fused connection units.

Visit our website: www.timeguard.com

Weathersafe Outdoor Power




WP2047

cknet

Single Gang Switched Socket

- 13 amp single gang switched socket.
- 4 x 20mm cable entries.
- Earth terminal and loop terminal in back box.
- Complies with BS1363.
- IP66 weatherproof rating.
- Impact resistant housing.
- Locking boss feature.

Part No. WP101



WP101

Single Gang Isolated Switched Socket

- 13 amp single gang switched socket.
- 4 x 20mm cable entries.
- Earth terminal and loop terminal in back box.
- Complies with BS1363.
- IP66 weatherproof rating.
- Impact resistant housing.
- Locking boss feature.
- Mains isolator switch ensures supply isolation before opening lid.

Part No. WP102

SIMPS
Safety Isolator Mains Protection Switch



WP102

Single Gang DP Fused Connection Unit

- 13 amp DP single gang switched fuse.
- 4 x 20mm cable entries.
- Fitted with 13A fuse link to BS1362.
- Earth terminal in back box.
- Complies with BS1363.
- IP66 weatherproof rating.
- Impact resistant housing.
- Locking boss feature.

Part No. WP103



WP103

Single Gang RCD Fused Connection Unit

- 4 x 20mm cable entries.
- Earth terminal and loop terminal in back box.
- Automatically disconnects both Live and Neutral connections leaving Earth connection intact.
- Extra fast action - trips out within 40 milliseconds (BS7288).
- Test button for safety checks.
- Complies with BS7288 and BS1363.
- Contacts remain latched when power supply is temporarily lost.
- IP66 weatherproof rating.
- Impact resistant housing.
- Locking boss feature.

Part No. WP104



WP104

WEATHERSAFE
IP66
R A T I N G

Single Gang TR610TOP DIN Timer

- Enclosed 24Hr/7 Day single channel (2 module size) 16(10)A digital timeswitch.
- Text Oriented Programming.
- 14 ON/OFF programmes per week.
- ON/OFF times may be repeated over a number of days without using extra memory locations.
- Automatic Summer/Winter changeover.
- Integral Lithium cell power reserve with 4 years life.
- Manual override to next programme change and permanent ON/OFF switching.
- 4 x 20mm cable entries.
- Earth terminal and loop terminal in back box.



**WP105/
WP106**

- Complies with BSEN60730.
 - IP66 weatherproof rating.
 - Impact resistant housing.
 - Locking boss feature.
- Part No. WP105**

Single Gang SEL170TOP DIN Solar Timer

Shares all the features of the WP105 Single Gang TR610TOP DIN Timer above, plus:

- Enclosed Solar Timeswitch.
- Precise astronomic calculation of sunrise and sunset times by entering date, time and location co-ordinates (latitude/longitude or country/city).
- Lights are switched ON and OFF according to sunrise and sunset times and can be shifted 120 minutes from these in either direction.
- Factory set time and date.
- 10 years battery reserve.
- Energy saving night switching.
- Daily switching times are presented graphically on the LCD by a bar chart.

Part No. WP106

Single Gang 2 Way Switch (SP)

- 10 amp (fluorescent rated) 1 gang SP 2-way.
- 4 x 20mm cable entries.
- Earth terminal and loop terminal in back box.
- Complies with BS3676.
- IP66 to BSEN 60529.
- Impact resistant housing.

Part No. WPL01



WPL01

Twin Gang 2 Way Switch (SP)

- 10 amp (fluorescent rated) 2 gang SP 2-way.
- 4 x 20mm cable entries.
- Earth terminal and loop terminal in back box.
- Complies with BS3676.
- IP66 to BSEN 60529.
- Impact resistant housing.

Part No. WPL02



WPL02

Single Gang Switch - Bell Push

- 10 amp (fluorescent rated) 1 gang SP 2-way.
- Push to make or push to break bell.

Part No. WPL03



**WPL03/
WPL04**

Single Gang DP Switch

- 10 amp (fluorescent rated) 1 gang DP 2-way press.

Part No. WPL04

Visit our website: www.timeguard.com

Outdoor Multi-Connector Box

Comes complete with a 4 way, 13 amp socket strip providing the ideal solution for outdoor plug-in power. Ideal for transformer linked garden lighting, fountain pumps, pool filters etc.

- Tough and durable housing.
- 1 x 20mm cable knock out (mains into socket strip).

- Up to 5 x cable seal outlets (to appliances).
- IP65 weatherproof rating.
- Keyhole slot for temporary locating and insitu alignment.
- Size: 335mm (H) x 220mm (W) x 107mm (D).
- **Part No. WP401**



Keyhole slot for temporary locating and in-situ alignment

Spacious design allowing for transformer storage

Tough, durable plastic housing

7 x case retaining screws and supports for rigidity and IP65 box seal

Multiple appliance cable outlets


IP65 weatherproof rating

4 gang socket strip suitable for all BS 13 amp plugs and selective timers (cable and plug not supplied)

Typical installation showing plugs, transformers and timers

Cable retaining bar for safe cable alignment

Ideal for all exterior seasonal lighting - whatever the weather!




Size:
335mm (H) x 220mm (W)
x 107mm (D)

WEATHERSAFE
IP65
RATING

3 THREE YEAR GUARANTEE



Visit our website: www.timeguard.com

Product Specifications



		WP101	WP102	WP103	WP104	WP105	WP106
Type		Switched	Isolated Switched	Spur Fused	RCD Fused	DIN Timer	Solar Timer
Operating Voltage	230V AC	•	•	•	•	•	•
Rocker Switch Poles		2	2	2			
Rocker Switch Rating	230V 13 Amp (3kW)	•	•	•	•	•	•
Operating Temperature	0° to 40° C	•	•	•	•	•	•
Integral BS1362 Fuse				•	•		
Trip Speed	BS7288 - 40ms				•		
RCD Contact Break	Double Pole				2 Pole		
Continues to Protect With	Lost neutral & pulsating DC earth fault				•		
Cable Capacity	3 x 2.5mm ²	•	•	•	•	•	•
Conforms To BS	BS1363, BS7288 (RCD)	•	•	•	•	BSEN60730	BSEN60730
Dimensions (mm)	Height x Width x Depth	130 x 135 x 80	130 x 135 x 80	130 x 135 x 80	130 x 135 x 80	130 x 135 x 80	130 x 135 x 80



		WP201	WP202	WP203	WP204	WP205	WP401
Type		Switched	Isolated Switched	Isolated Timer	RCD Latching	RCD	Connector Box
Operating Voltage	230V AC	•	•	•	•	•	•
Rocker Switch Poles		2	2		1	1	
Rocker Switch Rating	230V 13 Amp (3kW)	•	•	•	•	•	
Operating Temperature	0° to 40° C	•	•	•	•	•	•
Trip Speed	BS7288 - 40ms				•	•	
RCD Contact Break	Double Pole				2 Pole	2 Pole	
Continues to Protect with	Lost neutral & pulsating DC earth fault				•	•	
Cable Capacity	3 x 2.5mm ²	•	•	•	•	•	5 x 2.5mm ²
Conforms To BS	BS1363, BS7288 (RCD)	•	•	•	•	•	•
Dimensions (mm)	Height x Width x Depth	130 x 195 x 80	130 x 195 x 80	130 x 195 x 80	130 x 195 x 80	130 x 195 x 80	335 x 220 x 107



		WPL01	WPL02	WPL03	WPL04
Type	Single Gang	2 Way	2 Gang/2 Way	Bell	DP Switch
Operating Voltage	230V AC	•	•	•	•
Switch Rating 230V AC	10 A X	•	•	•	•
Operating Temperature	0° to 40° C	•	•	•	•
Cable Capacity	3 x 2.5mm ²	•	•	•	•
Conforms To BS	BS60669	•	•	•	•
Dimensions (mm)	Height x Width x Depth	92 x 92 x 64	92 x 92 x 64	92 x 92 x 64	92 x 92 x 64



Timeguard Limited

Victory Park, 400 Edgware Road, London NW2 6ND Tel: 020 8452 1112 Fax: 020 8450 0635

Email: csc@timeguard.com Website: www.timeguard.com