


LOCKING CIRCUIT BOARD SUPPORTS

Buy One or
Buy Bulk & SAVECBDLS Series
Double Locking Support

To Lock in Hole:
.156 (4.0)
Panel Thickness:
.062-.071 (1.6-1.8)


To Lock in Hole:
.187 (4.8)
Panel Thickness:
.031-.087 (0.8-2.2)

Specifications:

- Material: Nylon 6/6
- Color: Natural
- Flame Class: UL94 V-2

Item No.	A		Bulk Pack Qty.
	In	mm	
CBDLS305A	0.157	4.0	1000
CBDLS310A	0.197	5.0	1000
CBDLS315A	0.250	6.4	1000
CBDLS320A	0.276	7.0	1000
CBDLS325A	0.375	9.5	1000
CBDLS330A	0.394	10.0	1000
CBDLS335A	0.500	12.7	1000
CBDLS340A	0.625	15.9	1000
CBDLS345A	0.748	19.0	1000

Item No.	A		Bulk Pack Qty.
	In	mm	
CBDLS350A	0.787	20.0	500
CBDLS355A	0.866	22.0	500
CBDLS360A	1.000	25.4	500
CBDLS365A	1.125	28.6	500
CBDLS370A	1.181	30.0	500
CBDLS375A	1.378	35.0	500
CBDLS380A	1.496	38.0	500
CBDLS385A	1.772	45.0	500

LCBSA-6
Locking Circuit Board Support
High Temperature


Top Hole:
Snap-lock: .156 (4)
Panel Thickness:
.093 (2.4)

Bottom Hole:
Snap-lock: .187 (4.75)
Panel Thickness:
.078 - .141 (1.98 - 3.58)

- Maximum temperature of 392°F (200°C)
- Extremely high strength
- Strong, dependable grip
- Color: Natural
- Material: Nylon 6/6



Item No.	A		Bulk Pack Qty.
	In	mm	
Material: UL94 V-2	Material: UL94	Standoff Height	
LCBSA-6-3-01	LCBSA-6-3-19	3/16 (4.8)	1000
LCBSA-6-4-01	LCBSA-6-4-19	1/4 (6.4)	1000
LCBSA-6-5-01	LCBSA-6-5-19	5/16 (7.9)	1000
LCBSA-6-6-01	LCBSA-6-6-19	3/8 (9.5)	1000
LCBSA-6-7-01	LCBSA-6-7-19	7/16 (11.1)	1000
LCBSA-6-8-01	LCBSA-6-8-19	1/2 (12.7)	1000
LCBSA-6-10-01	LCBSA-6-10-19	5/8 (15.9)	1000
LCBSA-6-12-01	LCBSA-6-12-19	3/4 (19.1)	1000
LCBSA-6-14-01	LCBSA-6-14-19	7/8 (22.2)	1000
LCBSA-6-16-01	LCBSA-6-16-19	1 (25.4)	1000
LCBSA-6-18-01	LCBSA-6-18-19	1-1/8 (28.6)	1000
LCBSA-6-20-01	LCBSA-6-20-19	1-1/4 (31.7)	1000
LCBSA-6-22-01	LCBSA-6-22-19	1-3/8 (34.9)	1000

DLCBS3/CBDLS
Double Locking Support

To Lock in Hole:
.156 (4.0)
Panel Thickness:
.047-.071 (1.2-1.8)

To Lock in Hole:
.187 (4.8)
Panel Thickness:
.031-.087 (0.8-2.2)


Specifications:

- Material: Nylon 6/6
- Color: Natural
- Flame Class: UL94V-2

Item No.	A		Bulk Pack Qty.
	In	mm	
DLCBS3-3-01	0.187	4.8	1000
DLCBS3-4-01	0.250	6.4	1000
CBDLS215A	0.312	7.9	1000
DLCBS3-6-01	0.375	9.5	1000
DLCBS3-8-01	0.500	12.7	1000

Item No.	A		Bulk Pack Qty.
	In	mm	
DLCBS3-10-01	0.625	15.9	1000
CBDLS235A	0.750	19.1	1000
DLCBS3-14-01	0.875	22.2	1000
CBDLS245A	1.000	25.4	1000
CBDLS250A	1.125	28.6	1000

LCBS-7



Top Hole:
Snap-lock: .156 (4)
Panel Thickness:
.062 (1.57)

Bottom Hole:
Snap-lock: .187 (4.75)
Panel Thickness:
.031 - .078 (0.79 - 1.98)


Specifications:

- Material: Nylon 6/6
- Color: Natural



Item No.	A		Bulk Pack Qty.
	In	mm	
Material: UL94 V-2	Material: UL94 V-0	Standoff Height	
LCBS-7-3-01	LCBS-7-3-19	3/16 (4.8)	1000
LCBS-7-4-01	LCBS-7-4-19	1/4 (6.4)	1000
LCBS-7-5-01	LCBS-7-5-19	5/16 (7.9)	1000
LCBS-7-6-01	LCBS-7-6-19	3/8 (9.5)	1000
LCBS-7-7-01	LCBS-7-7-19	7/16 (11.1)	1000
LCBS-7-8-01	LCBS-7-8-19	1/2 (12.7)	1000
LCBS-7-10-01	LCBS-7-10-19	5/8 (15.9)	1000
LCBS-7-12-01	LCBS-7-12-19	3/4 (19.1)	1000
LCBS-7-14-01	LCBS-7-14-19	7/8 (22.2)	1000
LCBS-7-16-01	LCBS-7-16-19	1 (25.4)	1000
LCBS-7-18-01	LCBS-7-18-19	1-1/8 (28.6)	1000
LCBS-7-20-01	LCBS-7-20-19	1-1/4 (31.8)	1000
LCBS-7-22-01	LCBS-7-22-19	1-3/8 (34.9)	1000

LCBS-8



Top Hole:
Snap-lock: .156 (4)
Panel Thickness:
.062 (1.57)

Bottom Hole:
Snap-lock: .187 (4.75)
Panel Thickness:
.008 - .055 (0.2 - 1.4)

Specifications:

- Material: UL94 V-2 Nylon 6/6
- Color: Natural

Item No.	A		Bulk Pack Qty.
	In	mm	
LCBS-8-3-01	3/16 (4.8)	1000	
LCBS-8-4-01	1/4 (6.4)	1000	
LCBS-8-5-01	5/16 (7.9)	1000	
LCBS-8-6-01	3/8 (9.5)	1000	
LCBS-8-7-01	7/16 (11.1)	1000	
LCBS-8-8-01	1/2 (12.7)	1000	
LCBS-8-10-01	5/8 (15.9)	1000	

Item No.	A		Bulk Pack Qty.
	In	mm	
LCBS-8-12-01	3/4 (19.1)	1000	
LCBS-8-14-01	7/8 (22.2)	1000	
LCBS-8-16-01	1 (25.4)	1000	
LCBS-8-18-01	1-1/8 (28.6)	1000	
LCBS-8-20-01	1-1/4 (31.7)	1000	
LCBS-8-22-01	1-3/8 (34.9)	1000	