

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PREPARED, ILLINOIS

FED. MFR. CODE 91929

ASSEMBLY - PUSHBUTTON SWITCH

CATALOG LISTING

1PB73-T2

AR

1PB73-T2

PAGE 1 OF 1

M

DRAWING
NUMBER

6

ISSUE

REPLACES

RELEASE NO. ETS SR 9055

30 OCT 98

JAF

CHECK

26 MAY 60

KAC

14 JUNE 60

CCH

14 JUNE 60

60

26 MAY

60

60

60


60

60

60

60

60



NOTES

- (C) 1 - UNIT INCLUDES CAT. LIST "ISM" TYPE BASIC SWITCH
2 - TERMINALS ARE PLATED FOR SOLDERING
3 - RECOMMENDED FOR MANUAL OPERATION ONLY
4 - CONTACT MATERIAL - 24 K SOLID GOLD

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE - - - - 1 LB APPROX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
	BREAK DISTANCE .010 MIN 30 VOLTS DC RATING INDUCTIVE - - - - SEA LEVEL - - 1/2 AMP 50,000 FT. - - 1/2 AMP RESISTIVE - - - - SEA LEVEL - - 1 AMP 50,000 FT. - - 1 AMP MAXIMUM INRUSH - - - - 2 AMP	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1PB73-T2](#)