



DC Power Jack

163-4022 163-4026

KOBI CONN

DC Power Jack



Dimensions: In.

MATERIAL SPECIFICATIONS

Lug:	Nickel plated brass
Insulator:	Delrin
Contact Pin:	Nickel plated brass
Spring Contact:	Phosphor bronze
Nut:	Brass
Washer:	Brass
Body:	Brass

ELECTRICAL SPECIFICATIONS

Dielectric Strength:	500VAC
Insulation Resistance:	100MΩ min. @ 500VDC
Contact Resistance:	50mΩ max.
Power Rating:	1A @ 10VDC

Mouser Stock No.	Center Pin Dia.	Metal	Center Pin Length
163-4022	A	2.1mm, 1" bushing	7.5mm
163-4026	B	2.5mm, 1" bushing	7.5mm

Date Last Revised: 6/21/12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300000

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

163-4022 163-4026

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

163-4026 163-4022