


Knobs

450-KLN510, 450-KLN520, 450-KLN530,
450-KLN540, 450-KLN710, 450-KLN720,
450-KLN730, 450-KLN740, 450-KLN910
450-KLN920, 450-KLN125A, 450-KLN125B

Date Last Revised: 04/30/08



Dimensions: mm (in.)

Part Number	A	B	C	D	Color
450-KLN510	12.7 (.50)	9.5 (.374)	11.3 (.44)	3.2 (.125)	Natural
450-KLN520	12.7 (.50)	9.5 (.374)	11.3 (.44)	3.2 (.125)	Black
450-KLN530	12.7 (.50)	9.5 (.374)	11.3 (.44)	6.4 (.252)	Natural
450-KLN540	12.7 (.50)	9.5 (.374)	11.3 (.44)	6.4 (.252)	Black
450-KLN710	18.8 (.74)	15 (.59)	17.4 (.69)	3.2 (.125)	Natural
450-KLN720	18.8 (.74)	15 (.59)	17.4 (.69)	3.2 (.125)	Black
450-KLN730	18.8 (.74)	15 (.59)	17.4 (.69)	6.4 (.252)	Natural
450-KLN740	18.8 (.74)	15 (.59)	17.4 (.69)	6.4 (.252)	Black
450-KLN910	23.8 (.94)	18 (.71)	22.4 (.882)	6.4 (.252)	Natural
450-KLN920	23.8 (.94)	18 (.71)	22.4 (.882)	6.4 (.252)	Black
450-KLN125A	31.8 (1.252)	25 (.984)	30.4 (1.197)	6.4 (.252)	Natural
450-KLN125B	31.8 (1.252)	25 (.984)	30.4 (1.197)	6.4 (.252)	Black