


CEEform and SCHUKO® type receptacles, switched and interlocked, for zone 11



to DIN 49442, EN 60309-2, UNE-EN 60309-2. Colour: Electric grey and/or code colour.
Enclosure and insert made of **Amaplast**. Other voltages and frequencies on request.



1 MB 207 Amp.	16			32 63		
1 MB 180 Poles	3	4	5	3+4	5	4+5
Dim. in mm						
a	225	225	225	225	225	264
b	118	118	118	118	118	163
c	144	146	147	152	153	196
d	208	208	208	208	208	240
e	101	101	101	101	101	140
f	6,3	6,3	6,3	6,3	6,3	8,1
g	8	8	8	8	8	8
h	252	255	259	268	274	300
Pg	2x21	2x21	2x21	2x21	2x21	29
Pg*	2x21	2x21	2x21	2x21	2x21	2x29
Cond. cross section (mm²) min.-max.	1,5	1,5	1,5	2,5	2,5	6
Max. cable diam. (mm)	20,5	20,5	20,5	20,5	20,5	27


Receptacle

switched, with mechanical
DUO interlock

63A: **Soft-Contact**,
can be padlocked in the
OFF position

♦♦ IP 67

Product group 1074. Type 5113 shown.



Plano Amp.	125	
1 MB 177 Polos	4	5
Dim. en mm		
a	460	460
b	260	260
c	283	283
d	434	434
e	234	234
f	11	11
g	9	9
h	525	525
Pg	42	42
Pg*	2x42	2x42
Cond. cross section (mm²) min.-max.	25	25
Max. cable diam. (mm)	—70	—70


Receptacle

switched, with mechanical
DUO interlock

63A: **Soft-Contact**,
can be padlocked in the
OFF position

♦♦ IP 67

Product group 1074. Type 5692 shown.




Plano Amp.	16			32		
1 MB 206 Polos	3	4	5	3	4	5
Dim. en mm						
a	225	225	225	225	225	225
b	118	118	118	118	118	118
c	144	150	152	155	155	159
d	208	208	208	208	208	208
e	101	101	101	101	101	101
f	6,3	6,3	6,3	6,3	6,3	6,3
g	8	8	8	8	8	8
h	249	251	253	255	255	259
Pg	2x21	2x21	2x21	2x21	2x21	2x21
Pg*	2x21	2x21	2x21	2x21	2x21	2x21
Cond. cross section (mm²) min.-max.	1,5	1,5	1,5	2,5	2,5	2,5
Max. cable diam. (mm)	20,5	20,5	20,5	20,5	20,5	20,5

Receptacle

switched, with mechanical
DODSCH interlock

♦♦ IP 67

Product group 1087. Type 5132 shown.




Plano Amp.	63	
1 MB 178 Polos	4	5
Dim. en mm		
a	264	264
b	163	163
c	193	193
d	240	240
e	140	140
f	8,1	8,1
g	8	8
h	334	334
Pg	2x29	2x29
Pg*	2x29	2x29
Sección del conductor min.-máx. (mm²)	—25	—25
Max. cable diam. (mm)	27	27

Receptacle

switched, with mechanical
DODSCH interlock

♦♦ IP 67

Product group 1079. Type 5144 shown.




Drawing 1 MB 287
Dim. in mm

SCHUKO® type receptacle
switched, interlocked


♦♦ IP 67

Product group 1919. Type 10800 shown.



3 pole 4 pole 5 pole 3 pole 4 pole 5 pole 3 pole 4 pole 5 pole 3 pole 4 pole 5 pole
4h 4h 4h 6h 9h 9h 9h 6h 6h 7h 7h 7h

Part Numbers



Amps Poles
16 3
16 4
16 5

32 3
32 4
32 5

63 4
63 5

7011 7012
5599 5600 5601
5602 5603


5793 5604 5605 5606
5607 5608

5109 5110 5111
5112 5113

Std. Pack. Qty. g/each Weight
1 1060
1 1100
1 1150

1 1165
1 1180
1 1230


3 2530
3 2660



125 4
125 5

5887 5691 5690
5888 5692

1 7450
1 8250




16 3
16 4
16 5

32 3
32 4
32 5

5952 5698 5129 5130
5128 5132
5131 5133 5134 5137
5135 5136
5138 5139

4 920
4 995
4 1040

4 1060
4 1090
4 1180




63 4
63 5

5140 5141 5142
5143 5144

3 2560
3 2730

Part Number



16A, 230V, 2P+E

10800

4 625