



PRG.M0.8GL.LC65G

MECHANICAL DETAILS

Shell Style Model PR* : Free receptacle with cable collet


Keying 1 key (alpha=0; Plug: male contact; Receptacle: female contact)

Housing Material PSU (Polysulfone), gray

Cable Fixing 5.3 - 6.5 mm

Variant 2 G : Gray collet nut

	A	L
Mm.	14	40
In.	0.55	1.57



Available Download

[P_series_catalog.pdf](#)

PERFORMANCE DETAIL

Insert 1P.M08 : 8 Low Voltage

Insulator

Insulator




OTHER CHARACTERISTICS

Shell Style/Model Libellé

F ret (min): 50 N

F ret (max): 150 N

IP Rating 50



Related links

- [Contact](#)
- [Quote Request](#)
- [Catalogs Downloads](#)
- [Catalogs Requests](#)
- [Sample Request](#)
- [3D drawings](#)