





FEATURES

- Low Cost
- Ex-Stock Availability
- Industry Standard Dimensions
- Good Stability

APPLICATIONS

- Microprocessor Systems
- Datacommunications
- Consumer Electronics
- Automotive Electronics

STANDARD SPECIFICATION

Part Number	ZTT □.□□ MG	ZTT □.□□ MG	ZTT □.□□ MG	ZTT □.□□ MG	ZTT □.□□ MT	ZTT □.□□ MX
Frequency Range	2.00 ~ 2.99	3.00 ~ 3.49	3.50 ~ 4.99	5.00 ~ 6.99	7.00 ~ 13.00	13.01 ~ 25.00
Frequency Accuracy At 25°C	+/-0.5	+/-0.5	+/-0.5	+/-0.5	+/-0.5	+/-0.5
Temp. Stability -20°C to +80°C	+/-0.3	+/-0.3	+/-0.3	+/-0.3	+/-0.3	+/-0.3
Ageing (Over 10 years)	+/-0.3	+/-0.3	+/-0.3	+/-0.3	+/-0.3	+/-0.3
ESR (Ohms Max)	80	50	30	30	25	55
Max. Voltage	100V DC	100V DC	100V DC	100V DC	100V DC	100V DC
Insulation Resistance (Ohms)	5×10^{-8} Ohms (+10V DC)	5×10^{-8} Ohms (+10V DC)	5×10^{-8} Ohms (+10V DC)	5×10^{-8} Ohms (+10V DC)	5×10^{-8} Ohms (+10V DC)	5×10^{-8} Ohms (+10V DC)

TEST CIRCUITS

