




DRAWING NO
C-799288



NOTE

- MATERIAL
 - INSULATOR : GLASSFILLED THERMOPLASTIC POLYESTER
 - SLEEVE : BRASS
 - CLIP : STAMPED BERYLLIUM COPPER
- PLATING
 - SOLDER TAIL PLATING : 5µm Sn/Pb OVER 2-3µm Ni
 - CLIP PLATING : 3µm Sn/Pb OVER 2-3µm Ni
- INNER SPRING CONTACT ACCEPT Ø 0.40 TO 0.56 OR RECTANGULAR PIN 0.25 x 0.45
- MECHANICAL DATA WITH A Ø 0.43 TEST PIN :
 - INSERTION FORCE : 3.1N MAX.
 - EXTRACTION FORCE : 0.5N MIN.
 - MECHANICAL LIFE : 100 CYCLES MIN.

799288-1	COMPLETE ASSY PIN/INSULATOR
PART NO	DESCRIPTION

DIMENSIONS	mm							DRAWN S.CHANDEVault	30 SEP 98	THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FUTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM DSM SWITZERLAND.				
								CHECKED A. BOLIS	30 SEP 98					
SURFACE TEXTURE	N7/ (✓)							APPROVED P.-A. MEIER	30 SEP 98					
CONCENTRICITY	 0.15		0	FIRST ISSUE				CUSTOMER DRAWING FOR REFERENCE ONLY		NAME CLOSED FRAME .300" ELEVATED PIN DIP IC SOCKET – 16 POS.				
PRODUCT SPEC.		P	REV	ECN	DRWN	DATE	APVD							
 DSM DECOLLETAGE SA SAINT-MAURICE CH 1890 SAINT-MAURICE (VS)								LOC EK	SCALE 2/1	SIZE A4	DRAWING NO C-799288		SHEET 1 OF 1	REVISION O

WAS 98-63038-001