




COIL: @ +25 °C

RESISTANCE 600 OHMS ± 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.4 VDC

MUST RELEASE 1.5 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 4 MS MAX.

RELEASE 3 MS MAX.

CONTACT BOUNCE 3 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 4 AMPS 30 VDC
1 AMP 115 VAC 400 HZ
100,000 OPERATIONS MIN.

DR. R.B. 1/6/95 CK. 10/5/95

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. HI-G
CUST. NO. 2HA-2A-126

TYPE "HFW" RELAY

HFW4A1201S01