

HG 4000 E

Industrial Heat Guns



HG 4000 E Specifications

Item No.	35021 35031 with case
Temperature	80°F - 1100°F (27°C - 599°C)
Airflow	up to 21 cfm, 3000 Pa air pressure
Element	SmartChip™ DuraTherm™ ceramic heating element
Output	1750 watts
Voltage	120 VAC / 60 Hz
Amps	14.6
Power Cord	rubber construction, double insulated
Nozzle Diameter	1.2" (30.0 mm)
Net Weight	2.2 lbs (35.8 oz)
Dimensions	15.0" x 4.0" x 4.0" (l x w x d)
Single Sell Pack	dimensions: 18.0" x 5.0" x 5.0" weight: 3.4 lbs (54.4 oz)
Warranty	one year limited
Certifications	C-UL-UL Listed, RoHs Compliant, ISO 9001:2001 Made in E.U.

HG 4000 E IntelliTemp™ Heat Gun with LED Temperature Display (120V)


STEINEL HG 4000 E features a continuously variable temperature and airflow regulator, a digital display of actual and selected temperature, an intelligent motor control system, a brushless motor and a plug-in easy to change element. With pinpoint accuracy the HG 4000 E in conjunction with the appropriate nozzle is ideal for welding copper and plastics.

Applications

Flooring, roofing, avionics, shrink wrapping, activating adhesives, softening compounds, window tinting, bending plastics and other applications requiring long life and even heat

Key Features:

- Powerful 120 V heat gun with 21 cfm output
- Airflow and temperature continuously variable
- Easy-to-ready LED display
- Durable heavy duty housing
- Power cord can be changed without opening enclosure
- Straight form for optimum stationary use
- Field changeable element
- Factory sealed brushless motor
- Smartchip™ technology allows the gun to stay calibrated with new element



Brushless DC Motor



3 Stage Air Control



SmartChip™ Plug-In
DuraTherm Heating Element



Field Changeable Element



Field Changeable Element



www.steinell.net

HG 4000 E

Industrial Heat Guns

STEINEL®
PROFESSIONAL

Industry Specific Kits Available



Heavy Duty Metal Case
17.9" x 5.4" x 10.2"
No. 40090



Accessories for a Variety of Applications



40 mm Angle Flathead Slit
4.3" x 1.8" x 1.5"
No. 09201



20 mm Angle Flathead Slit
3.8" x 1.8" x 1.3"
No. 09211



5 mm Reducer Nozzle
3.1" x 1.3" x 1.3"
No. 09221



10 mm Reducer Nozzle
3.1" x 1.3" x 1.3"
No. 09231



90° Corner Nozzle
2.6" x 2.6" x 1.3"
No. 09241



High Speed Welding Tip
(Fits on 5 mm Reducer)
No. 09183



Feed Roller
6.5" x 1.8" x 1.0"
No. 09037



Roller with Ball Bearings
45 mm Silicone Seam Roller
No. 01250



Lathe
Jointing planer
No. 09311



Groover
7.7" x 2.0" x 1.3"
No. 09010



Quarter Moon Knife
8.8" x 5.0" x 1.4"
No. 09030



Trim Guide
2.1" x 2.1" x 0.3"
No. 09025



Scriber
6.1" x 1.7" x 0.6"
No. 09080



Diamond Sharpener
6.7" x 2.7" x 1.3"
No. 09060