

Home > LED Panel Indicators > LED Panel Indicators, Relampable > Cylindrical Lens Single-LED

LED Lamps, Panel Mount, 11/16" (17.5mm) Mtg. Dia Relampable; Fluted Lens

1-Chip, Sunlight-Visible, Clear Cylindrical Lens Indicators




Dome Lens Single-LED

Cylindrical Lens Single-LED

Dome Lens; Lower Cost Plastic Holder

Cylindrical Lens; Lower Cost Plastic Holder



3 YEAR WARRANTY

Standard Assembly Consists of:

Lens Cap LCF780-xxx; Lamp BF321-0xx; Holder HLDR-BS780

White LED technology is patent protected in the US. LEDtronics White LED products are covered under these patents.


All Series under this Category:

BSF780 11/16" Cylindrical Lens Indicators Assembly

LENS-LCF780 Flat, Cylindrical Lens

HLDR-BS780 Lamp Holders

BSF780 Series Relampable 11/16" Indicators; Cylindrical Lens, Metal Holders



Flat, Cylindrical Lens Single LED

24/28 Vdc


Electrical-Optical Characteristics (Ta = 25°C)										
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Input Voltage, V (typ)	Current (A)	Maximum Candela	Operating Temperature	Color Temp. (Kelvin)	λ _p , nm	LED Emitting Color
TO ORDER, CALL US @ 800-579-4875	BSF780-0CW-028B	CALL		24/28Vdc (@28Vdc)	0.012-0.015 A	0.300cd	~30°C to ~+50°C	8000K		Cool White
TO ORDER, CALL US @ 800-579-4875	BSF780-0AG-028B (15RE)	CALL		24/28Vdc (@28Vdc)	0.012-0.015 A	--	~30°C to ~+50°C		525nm	Super Aqua Green

120 VAC

Electrical-Optical Characteristics (Ta = 25°C)										
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Input Voltage, V (typ)	Current (A)	Maximum Candela	Operating Temperature	Color Temp. (Kelvin)	λ _p , nm	LED Emitting Color
TO ORDER, CALL US @ 800-579-4875	BSF780-0CW-120A	CALL		120VAC	0.006-0.008 A	0.150cd	~30°C to ~+50°C	8000K		Cool White
TO ORDER, CALL US @ 800-579-4875	BSF780-0UR-120A (7R)	CALL		120VAC	0.006-0.008 A	0.045cd	~30°C to ~+50°C		660nm	Ultra Red
TO ORDER, CALL US @ 800-579-4875	BSF780-0AG-120A (RoHSVC120108)	CALL		120VAC	0.006-0.008 A	--	~30°C to ~+50°C		525nm	Super Aqua Green

††Full Beam Width at 50% Intensity

LENS-LCF780 Series Flat, Cylindrical Lens Caps



CAUTION: WHITE LEDS used with COLORED LENSES; A cool white LED when used to illuminate a colored lens will result in less than optimal color quality and intensity — but white LED lamps may be preferred by certain customers who want to limit their parts inventory.


Flat, Cylindrical Lens Caps

Electrical-Optical Characteristics (Ta = 25°C)				
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Lens Cap Color
ADD TO CART	LENS-LCF780-CWF (FND)	ea	25	Waterclear
ADD TO CART	LENS-LCF780-TWF (SAME AS TW)P.C. UL94V-2 (29RE)	ea	25	Diffused White
ADD TO CART	LENS-LCF780-CRF (29RE)	ea	25	Clear Red
ADD TO CART	LENS-LCF780-CAF (29RE)	ea	25	Clear Orange
TO ORDER, CALL US @ 800-579-4875	LENS-LCF780-CYF (29RE)	CALL		Clear Yellow
ADD TO CART	LENS-LCF780-CGF (29RE)	ea	25	Clear Green
Call 800-579-4875 To ORDER		Click For Volume Discount Thru Distributor		

HLDR-BS780 Series Lamp Holders for 11/16" (17.5mm) Mounting Holes


(7.62mm) Maximum panel thickness

Silver Body, with Spade Terminals




Electrical-Optical Characteristics (Ta = 25°C)				
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Description
ADD TO CART	HLDR-BS780 (HOLDER, CHROME, SLDR LUG (38RE))	ea	10	Silver Body; Spade Terminals
Call 800-579-4875 To ORDER		Click For Volume Discount Thru Distributor		

Silver Body, with Screw Terminals




Electrical-Optical Characteristics (Ta = 25°C)				
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Description
ADD TO CART	HLDR-BS780S (HOLDER, CHROME, SCRW TERM (84RE))	ea	10	Silver Body; Screw Terminals
Call 800-579-4875 To ORDER		Click For Volume Discount Thru Distributor		

Watertight, Silver Body, with Spade Terminals




Electrical-Optical Characteristics (Ta = 25°C)				
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Description
ADD TO CART	HLDR-BS780-WP (HLDR, CHROME, SLDR LUG, WATER PROOF (RE))	ea	10	Silver Body; Spade Terminals; Watertight
Call 800-579-4875 To ORDER		Click For Volume Discount Thru Distributor		

Watertight, Silver Body, with Screw Terminals




Electrical-Optical Characteristics (Ta = 25°C)				
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Description
ADD TO CART	HLDR-BS780S-WP (HLDR, CHROME, SCRW TERM, WATERPROOF (RE))	ea	10	Silver Body; Screw Terminals; Watertight
Call 800-579-4875 To ORDER		Click For Volume Discount Thru Distributor		

Black Body, with Spade Terminals




Electrical-Optical Characteristics (Ta = 25°C)				
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Description
TO ORDER, CALL US @ 800-579-4875	HLDR-BS780B (HOLDER, BLACK, SLDR LUG (RE))	CALL		Black Body; Spade Terminals

Black Body, with Screw Terminals



Electrical-Optical Characteristics (Ta = 25°C)				
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Description
ADD TO CART	HLDR-BS780BS (HOLDER, BLK, SCRW TERM (38RE))	ea	10	Black Body; Screw Terminals
Call 800-579-4875 To ORDER		Click For Volume Discount Thru Distributor		

Watertight, Black Body, with Screw Terminals



Electrical-Optical Characteristics (Ta = 25°C)				
CLICK TO ORDER	PART NO. (DESCRIPTION)	PRICE	MIN BUY	Description
ADD TO CART	HLDR-BS780BS-WP (HOLDER, BLK, SCRW TERM, WTRPROOF (15RE))	ea	10	Black Body; Screw Terminals; Watertight
Call 800-579-4875 To ORDER		Click For Volume Discount Thru Distributor		

All specifications and pricing subject to change without notice.

Options: For qualified applications and large quantity orders

- Three Year Warranty
- AC types available for OEM applications.
- Other voltages available for OEM application.
- Intensity & Angle shown for LED used. Fluted Lens will reduce Intensity but increase Angle of View.

Indoor Lighting Products	Outdoor Products	Standard LED Products	Products By Industry
T8 Tube Lights CFL Style Bulbs PAR Style Bulbs Chandelier Bulbs Classic Style Bulbs MR Style Bulbs Low Voltage Tube Lights	Cobrahead Street Lights Shoobox Area Lights Flood Lights & Wall Packs High Bay Lights Gas Station Canopy Lights Post Top Lamps Modular Street Lights	Miniature Based LEDs Panel Mount Indicators PC Board LEDs Exit Sign & Beacon Bulbs SMD & Discrete LEDs Relampable Panel Indicators Intermediate Automotive Bulbs	Power Plant & Utilities Lights Transportation & Railroad Lights Elevator Industry Lights Traffic & Signal Lights Solar Panels & Products Safety Vests & Lights LEDtronics NSN LEDs

LEDtronics, Inc.

Site Map Privacy Policy Warranty Contact Us LED News

23105 Kashiwa Ct, Torrance, CA 90505 - PH: (800) 579-4875/(310) 534-1505 - FAX: (310) 534-1424

All images and pictures and text on our website is Copyrighted property of LEDtronics. No-one is authorized to use our pictures, images, catalogs or text without our explicit written approval.

Copyright © 1997-2013 LEDtronics, Inc., All Rights Reserved.