




FEATURES:

- Accepts .080 pin tip plugs
- Mounts in panels up to .250" thick.

MATERIAL:

Insulation – Polycarbonate - Molded to pin tip jack body

Lockwasher, #8 Internal Tooth – Steel - Nickel plated

Hex Nut, #8-32 – Brass – Nickel plated

Pin Tip Jack Body: Brass – Gold plated

RATINGS:

Operating Temperature: +115°C. (+239°F.) Max.

Operating Voltage: 1500 VDC

Current: 5 Amperes.

ORDERING INFORMATION: Model 3542-*

*=Color Code – See Tabulation Block

Sold in packages of 10

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90193 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3542-8](#) [3542-1](#) [3542-7](#)