

Cable Lug 32/35 mm DIN-Rail Terminals

Feed Through

The Weidmüller SAKG range offers the following connection variations:


- Clamping yoke connection, Version III. The stripped conductor can be connected without further preparation.
- Lug connection, Version II.
 - Two types of screw connection are provided here.
 - a) Screw set with lock nut
 - b) with thread in the busbar
- Clamping yoke/lug connection as a combination, Version I.




Version I



Version II
without thread



Version II G
with thread




Version III

Cables with cable lugs are connected to Version I SAKG terminals and SS stud terminals.



Fitting instructions for SAKG terminals

When tightening the clamping screw, it is recommended that the conductor be held against the tightening direction in order to avoid any deformation of the mounting rail and to keep the terminal foot free of torsional forces.



Cover

In order to ensure shock protection following connection of the conductors, Type AH hoods can be snapped onto the terminal.

		SAKG 28 I		SAKG 28 II	
					

See Accessories section for mounting rails, end brackets, test taps, additional marking material and accessories.