




DESCRIPTION: HIGH DENSITY FEMALE - VERTICAL DIP - LOW PROFILE - STAMPED

44 PIN SHOWN



MATERIAL:

- SHELL: STEEL, NICKEL PLATED
- INSULATOR: PBT, UL 94V-O RATED, 230°C PROCESS TEMP
- CONTACT: PHOSPHOR BRONZE, GOLD FLASH ENTIRE CONTACT

ELECTRICAL:

- CURRENT RATING: 2 AMPS
- WITHSTANDING VOLTAGE: 1,000VAC AT SEA LEVEL
- CONTACT RESISTANCE: 10 mOhms Max.
- INSULATION RESISTANCE: 5,000 MOhms min.
- VOLTAGE: 500VAC FOR 1 MINUTE
- TEMPERATURE: -55° C TO +125° C

RoHS COMPLIANT

No. OF PINS	DIMENSIONS			
	A	B	C	D
15	1.214	0.984	0.405	0.090
	30.80	24.99	10.29	2.29
26	1.545	1.312	0.765	0.090
	39.24	33.32	19.43	2.29
44	2.088	1.852	1.305	0.090
	53.04	47.04	33.15	2.29
62	2.730	2.500	1.948	0.095
	69.34	63.50	49.47	2.41
78	2.635	2.406	1.805	0.095
	66.93	61.11	45.85	2.41

4 ROWS

195-YYY-2 1 3 L YY 1

SERIES

POSITIONS

015

026

044

062

078

GENDER

2 = FEMALE

TERMINATION

1 = PC MOUNT

SHELL PLATING

3 = NICKEL

RoHS COMPLIANT

LOW PROCESS TEMP. - 230°C

HARDWARE OPTIONS

00 = NO HARDWARE

03 = 4-40 HEX STANDOFFS

55 = 4-40 INSERTS

PLATING OPTIONS

1 = GOLD FLASH

DO NOT SCALE FROM DRAWING

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: PAM JENKINS

CHECKED:

DATE: 09-12-05

DATE:






NorComp

SCALE: 1 : 1

SHEET 1 OF 3

REV 5

DWG NO. 195-YYY-213LYY1



HIGH DENSITY
VERTICAL


* TYP. ON ALL SIZES

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 03-09-06	
			CHECKED:		DATE:	
	NorComp		SCALE: FULL		SHEET 2 OF 3	
		DWG NO.		REV 5		
				195-YYY-213LYY1		

TOLERANCE:
ALL DIMENSIONS ARE ±0.010

55X 0.158" (BOARD SIDE)



03X 0.158" (BOARD SIDE) - 0.230" MATING SIDE



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

DATE:
12-21-09

CHECKED:

DATE:

NorComp

SCALE:	SHEET 3 OF 3	REV 5
--------	--------------	-------

DWG NO.	195-YYY-213LYY1
---------	-----------------

RoHS COMPLIANT