





Rev	AWO #	Description	Date	Appr
-	7155	RELEASED	10/09/06	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Hi Temp thermoplastic, glass reinforced,
rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Steel, Nickel plated

Plating:

Gold flash over Nickel underplate on Contact area,
Tin over Nickel underplate on SMT tails

Electrical:

Operating voltage: 40 VAC max

Current rating: 0.5 Amps max

Contact resistance: 30 mOhms max

Insulation resistance: 10 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -20°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES Holes	
X	± .10 ØX ± .10
.XX	± .020 ØXX ± .015
.XXX	± .015 ØXXX ± .010

ADAM TECH	
909 Rahway Avenue, Union, NJ 07083	
Phone: 908-687-5000 Fax: 908-687-5710	
TITLE	
HDMI CONNECTOR, RIGHT ANGLE, SURFACE MOUNT, NO PEG, FLANGE	

APPROVALS	
DRAWN	BW
CHECKED	
APPROVED	

SIZE	PART NO.	REV.
X	HDMI-S-RA-TSMT	-
REF:	SCALE: NTS	SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADAM TECH:](#)

[HDMI-S-RA-TSMT-MF](#)