


**Heavy Duty AC Rated Toggle Switches**

General Purpose switches rated at 15 amps, 125 VAC and 28 VDC and 10 amps at 250 VAC. UL listed and CSA certified in single, double, three and four pole configurations. All are rated 1/4 H.P. — 15/32" bushing — 11/16" Toggle.



Stock No.	Mfr.'s Type	Switch Action	Terminals	EACH			
				1-24	25-99	100-499	500-999
683-0048 683-0049	2FA53-73 2FA53-73-TABS	S.P.S.T. ON-NONE-OFF S.P.S.T. ON-NONE-OFF	Solder Spade	3.59 3.59	2.77 2.77	2.43 2.43	2.13 2.13
683-0050 683-0051 683-0052	2FA54-73 2FB53-73 2FB53-73-TABS	S.P.S.T. ON-NONE-OFF S.P.D.T. ON-NONE-ON S.P.D.T. ON-NONE-ON	Screw Solder Spade	4.11 4.41 4.41	3.18 3.43 3.43	2.79 3.01 3.01	2.79 2.64 2.64
683-0053 683-0054	2FB54-73 2FC53-73	S.P.D.T. ON-NONE-ON S.P.D.T. ON-OFF-ON	Screw Solder	5.19 4.41	4.02 3.43	3.53 3.01	3.09 2.64
683-0055 683-0056 683-0057	2FC53-73-TABS 2FC54-73 6FC54-73*	S.P.D.T. ON-OFF-ON S.P.D.T. ON-OFF-ON S.P.D.T. ON-OFF-ON	Spade Screw Screw	4.41 5.19 7.22	3.43 4.02 5.59	3.01 3.53 4.90	2.64 3.09 4.30
683-0058 683-0059	2GK50-73 2GK51-73	D.P.S.T. ON-NONE-OFF D.P.S.T. ON-NONE-OFF	Solder Spade	5.68 5.68	4.41 4.41	3.87 3.87	3.39 3.39
683-0060 683-0061 683-0062	2GK54-73 2GL50-73 2GL51-73	D.P.S.T. ON-NONE-OFF D.P.D.T. ON-NONE-ON D.P.D.T. ON-NONE-ON	Screw Solder Spade	6.73 6.79 6.79	5.22 5.26 5.26	4.58 4.62 4.62	4.02 4.05 4.05
683-0063 683-0064	2GL54-73 2GM50-73	D.P.D.T. ON-NONE-ON D.P.D.T. ON-OFF-ON	Screw Solder	8.34 6.79	6.47 5.26	5.67 4.62	4.97 4.05
683-0065 683-0066 683-0067	2GM51-73 2GM54-73 HK250-73	D.P.D.T. ON-OFF-ON D.P.D.T. ON-OFF-ON 3.P.S.T. ON-NONE-OFF	Spade Screw Solder	6.79 8.34 10.43	5.26 6.47 8.08	4.62 5.67 7.09	4.05 4.97 6.21
683-0068 683-0069	HK251-73 HK254-73	3.P.S.T. ON-NONE-OFF 3.P.S.T. ON-NONE-OFF	Spade Screw	10.43 12.34	8.08 9.57	7.09 8.39	6.21 7.36
683-0070 683-0071 683-0072	HL250-73 HL251-73 HL254-73	3.P.D.T. ON-NONE-ON 3.P.D.T. ON-NONE-ON 3.P.D.T. ON-NONE-ON	Solder Spade Screw	12.82 12.82 15.34	9.93 9.93 11.89	8.71 8.71 10.43	7.64 7.64 9.15
683-0073 683-0074	HM250-73 HM251-73	3.P.D.T. ON-OFF-ON 3.P.D.T. ON-OFF-ON	Solder Spade	12.82 12.82	9.93 9.93	8.71 8.71	7.64 7.64
683-0075 683-0076 683-0077	HM254-73 IK250-73 IK251-73	3.P.D.T. ON-OFF-ON 4.P.S.T. ON-NONE-OFF 4.P.S.T. ON-NONE-OFF	Screw Solder Spade	15.34 14.30 14.30	11.89 11.08 11.08	10.43 9.72 9.72	9.15 8.52 8.52
683-0078 683-0079	IK254-73 IL250-73	4.P.S.T. ON-NONE-OFF 4.P.D.T. ON-NONE-ON	Screw Solder	15.87 17.46	12.30 13.53	10.79 11.86	9.46 10.40
683-0080 683-0081 683-0082	IL251-73 IL254-73 IM250-73	4.P.D.T. ON-NONE-ON 4.P.D.T. ON-NONE-ON 4.P.D.T. ON-OFF-ON	Spade Screw Solder	17.46 20.99 17.46	13.53 16.28 13.53	11.86 14.28 11.86	10.40 12.52 10.40
683-0083 683-0084	IM251-73 IM254-73	4.P.D.T. ON-OFF-ON 4.P.D.T. ON-OFF-ON	Spade Screw	17.46 20.99	13.53 16.28	11.86 14.28	10.40 12.52

\*Momentary on action.

**Nylon Insulated Toggle Switches**


Series D switches have self-cleaning wiping action contacts suitable for both power and low-level switching nylon flat or bat lever actuators and bushing/frame super structure for double insulated requirements. UL listed, CSA certified. Series rated at 10 amps 125 VAC, 5 amps 250 VAC, 1/2 H.P. 125-250 VAC, 10 amps 28 VDC.

**Paddle Toggle Actuator**

Stock No.	Mfr.'s Type	Switch Action	Terminals	EACH			
				1-24	25-99	100-499	500-999
683-0085	DA100-PB-B	S.P.S.T. ON-NONE-OFF	Solder/Spade	2.44	1.90	1.66	1.46
683-0086	DA105-PB-B	S.P.S.T. ON-NONE-OFF	Wire	3.57	2.77	2.43	2.13
683-0087	DB100-PB-B	S.P.D.T. ON-NONE-ON	Solder/Spade	2.73	2.12	1.86	1.63
683-0088	DC100-PB-B	S.P.D.T. ON-OFF-ON	Solder/Spade	2.73	2.12	1.86	1.63

**Bat Toggle Actuator**

683-0089	DA100-BB-B	S.P.S.T. ON-NONE-OFF	Solder/Spade	2.44	1.90	1.66	1.46
683-0090	DA105-BB-B	S.P.S.T. ON-NONE-OFF	Wire	3.57	2.77	2.43	2.13



**General Purpose Pushbutton Switches**

Slow make/slow break momentary AC only. Circuitry: On-none-off. UL listed and CSA certified (P26A-1D-RND and P26L-1D-RND not shown).

**6 Amps 125 VAC — 3 Amp 250 VAC**

Stock No.	Mfr.'s Type	Switch Action	Terminals	Cap	EACH			
					1-24	25-99	100-499	500-999
683-0093	P26A-1D-RND	S.P.N.O.	Solder	Metal	5.48	4.24	3.72	3.26
683-0094	P26L-1D-RND	S.P.N.C.	Solder	Metal	5.48	4.24	3.72	3.26
683-0095	P27A-BL	S.P.N.O.	Solder	Black	4.93	3.81	3.35	2.93
683-0097	P27L-BL	S.P.N.C.	Solder	Black	4.93	3.81	3.35	2.93

**15 Amps 125 VAC — 10 Amps 250 VAC**

683-0099	170	S.P.N.C.	Screw	Metal	8.65	6.71	5.89	5.16
683-0100	172	S.P.N.O.	Screw	Metal	8.65	6.71	5.89	5.16

**Quick Make/Quick Break Maintained AC/DC; 6 Amps 125 VAC — 3 Amps 250 VAC**

683-0101	110-SP	S.P.S.T.	Screw	Metal	7.81	6.06	5.31	4.66
683-0102	111-16P	S.P.S.T.	Wire	Metal	7.81	6.06	5.31	4.66

