

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130106-0119](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway™ Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets with Guards, Overall Length 7.62m (50.0')

Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130106](#)
NEMA Configuration NEMA L5-15
NEMA Rating Rain Tight
Outlet None
Overview [Stringlights](#)
Product Literature Order No 987650-8055
Product Name Super-Safeway™
Type String Lights
UPC 78678879900
Woodhead Yes

Physical

Cord Length - Primary 1.52m (5.0')
Cord Length - Secondary 1.52m (5.0')
Depth 47.625mm (1.875")
Duty Industrial
Guard Included 377
Guard Type N/A
Height 107.95mm (4.250")
Length 15.24m (50.0')
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Stringer
Packaging Type Carton
Socket Construction Rubber Molded

Electrical

Bulb Type Incandescent
Cord Type - Primary 12/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 200W
Lumens 2000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number 323536



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130106Series](#)