



DESCRIPTION: 97 SERIES SOLDER STYLE PANEL & CABLE MOUNT
D-SUB CONNECTORS

MODEL NUMBER: 40-97XXS

APPLICATION: FOR CABLE

CRIMP TOOL: N/A


IMPEDANCE: N/A

FEQUENCY RANGE: 0-15 MHz


MATERIAL: HOUSING STEEL NICKEL PLATED
INSULATOR PBT+FIBER-GLASS UL94-V0 WHITE
CONTACT COPPER-ALLOY, GOLD PLATED

RoHS COMPLIANCE: YES

TECHNICAL DETAIL: N/A



MODEL NUMBER	PIN	A	B	C	D
40-9709S	09	30.80	24.99	16.30	19.20
40-9715S	15	39.15	33.32	24.65	27.70
40-9725S	25	53.00	47.04	38.40	41.10
40-9737S	37	69.30	63.50	54.80	57.30



DIM OUTLINE

This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	RoHS ☒ 2002/95/EC UNLESS OTHERWISE SPECIFIED UNITS: METRIC .XX ±.51 .XXX ±.127 ANGLES ±2°	AIM-Cambridge Title: D-Sub Connector, 97 Series, Solder Style Panel and Cable Mount, Female			
		Model No. 40-97XXS			
		Size A	DO NOT SCALE DRAWING	Date: 9/9/2013	Sheet 1 of 1