

VANSONIC ENTERPRISE CO., LTD.

8F.,No.7,Lane 16, Sec.2, Szechwan Road, Panchiao, Taipei Hsien, TAIWAN.


TEL: +886-2-29626335

FAX: +886-2-29625220

E-MAIL: vansonic@ms4.hinet.net

1.	MODEL:	34KC08-1									
2.	Dimension	Outer Diameter 34x34 mm.				Baffle Opening ø28.5 mm.					
		Height		Refer to Drawing		Weight		26.6 Grams.			
3.	Magnet	Materials		Rare Earth			Size		ø 19 x 3.4 mm.		
4	Nominal Resistance	8	Ω	±	15	%					
5.	Power Rating	Normal		3		W.		Maximum		5 W.	
6.	Lowest Resonant Frequency	170			±		20		%		Hz.
7.	Output Sound Pressure Lever (S.P.L.)	82		±		3 db / 1.0 Watt		. 0.5 Meter.			
		Average at			600,		800,		1000,		1200 Hz.
8.	Frequency Range	120		~		20000 Hz.		Average S P L - 10 db.			
9.	Distortion	5	%		Maximum At		1000 Hz.		1		W.
10.	Abnormal Sound Test	Must be Normal Tested By					4.9 Volts.		Sine Wave.		
11.	Load Test	White Noise with Weighted Filter					4.9 Volts.(RMS)		24 Hrs.		
12.	Polarity	Diaphragm shall move Forward when Apply a Positive DC.									
		Current to the "+" or "Marked" Terminal.									


MOUNTING NOTICE



Unit : mm

Housing Material : PBT

34KC08-1 VOL:2.828V(1W) DIS:0.5M VANSONIC
X:1.0000kHz *Y:82.63dB ZA:1.0000 SSR Fund.



14-AUG-2001 15:20:24

Mode: SSR

