



HelaGuard Accessories

• A90FM 90° Elbow

Internal and external threads, nickel plated brass.



HelaGuard A90FM 90° Elbow.

Technical Table

Article-No.	Type	Thread Size (metric)	Thread Size (PG)	Pack Cont.
166-50000	A90FM-PG7	–	PG7	10
166-50001	A90FM-M16	M16	–	10
166-50002	A90FM-M20	M20	–	10
166-50003	A90FM-M25	M25	–	10
166-50004	A90FM-M32	M32	–	2
166-50005	A90FM-M40	M40	–	1
166-50006	A90FM-M50	M50	–	1

All dimensions in mm. Subject to technical changes.

Material Data

Material	Nickel Plated Brass (NPB)
Colour	Metal (ML)
Operating Temperature	-100 °C to +300 °C



• ACP Couplers

Internally threaded, nickel plated brass.



HelaGuard ACP Couplers.

Technical Table

Article-No.	Type	Thread Size (metric)	Pack Cont.
166-50400	ACP-M16	M16	10
166-50401	ACP-M20	M20	10
166-50402	ACP-M25	M25	10
166-50403	ACP-M32	M32	10
166-50404	ACP-M40	M40	2
166-50405	ACP-M50	M50	1
166-50406	ACP-M63	M63	1
166-50407	ACP-M75	M75	1

All dimensions in mm. Subject to technical changes.

Material Data

Material	Brass
Colour	Metal (ML)
Operating Temperature	-100 °C to +300 °C

