


Part
number

DM537435001NC

DM 53743-5001 NC	Socket coaxial contacts	1.70	2.46	3.13	3.84	RG 179 BU RG 316 BU
contact ref.	Designation	$\phi A^{+0.10}_0$	$\phi B^{+0.05}_0$	$\phi C^{+0.10}_0$	$\phi D^{+0.10}_0$	cable ref

European Views

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101		projection mm	size A3		Scale 5
		TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR		LINEAR		ECN L506-0097
Dr	BOUITIER	1991/09/30	0.X		±0.1	0.XX		±0.1
Eng	PESSON	1991/09/30	0.XX		±0.1	0.XXX		±0.1
Chr	LEGARE	1991/09/30	0.XX ±2°			Product family		D-SUB
Appr	LEGARE	1991/09/30	Product family		D-SUB	Spec ref -		
FCI		title		SOCKET COAXIAL CONTACT RI		C-8639-515		Rev. E
		catalog no		-		CUSTOMER		sheet 1 of 1

rev	ecn no	dr	date
B	-	MAS	2000/08/16
C	LS05-0026	MPE	2005/07/08
D	LS05-0084	MPE	2005/09/28
E	LS06-0097	LGO	2006/07/25
-	-	-	-
-	-	-	-
-	-	-	-