



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
 - 600V MAX. VOLTAGE RATING.
 - 221°F (105°C) MAX. TEMP. RATING (CSA).
 - 257°F (125°C) MAX. TEMP. RATING (UL).
 - STRANDED COPPER WIRE ONLY.
- MATERIAL:
 - STAMPING-CDA 260 BRASS, NICKEL PLATED
 - HOUSING-TYPE 6/6 NYLON
- DIMENSIONS IN BRACKETS ARE IN mm OR mm²
- COLORS ARE TRANSLUCENT
- WIRE STRIP LENGTH: 9/32 ^{+1/32}₋₀ (7.1 ^{+0.8}₋₀)
- SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.



PART NUMBER	TAB SIZE	WIRE RANGE AWG	COLOR (note 4)	MAX. INSUL.	DIMENSIONS in			CRIMP TOOLS
					A ±.03	B ±.02	C ±.02	
DNF18-250F1M	.250 X .032 (6.3 X 0.8)	22-18 (0.5-1.0)	RED	.133 (3.38)	.90 (22.9)	.42 (10.7)	.27 (6.9)	CT-100A* (*DNF18 ONLY) CT-520 CT-600-A CT-1525 CT-2500
DNF14-250F1M	.250 X .032 (6.3 X 0.8)	16-14 (1.5-2.5)	BLUE	.158 (4.01)	.90 (22.9)	.42 (10.7)	.27 (6.9)	



LISTED
587H
E52164



CERTIFIED
LR31212

						PANDUIT CORP. TINLEY PARK, ILLINOIS				
						LOOSE PC. FULLY INSULATED MALE DISCONNECT .250 X .032				
08	8/11	SHOR	MODIFIED NOTE #6, ADDED CRIMP TOOLS							
REV	DATE	BY	DESCRIPTION		PM	CUST	DRAWN BY	CHK'D	SCALE	DRAWING NO.
							JV	LM		A41325