

Indoor/Outdoor Vinyl for Lean, Facility & Safety ID and General ID.

Continued from previous page.




Figure 33



Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels/Roll
B-595 Indoor/Outdoor Vinyl Film							
Fig. 33	XC-500-595-CL-BK	B-595	Vinyl	BK on CL	0.500 (12.7)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-750-595-CL-BK	B-595	Vinyl	BK on CL	0.750 (19.1)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-1000-595-CL-BK	B-595	Vinyl	BK on CL	1.000 (25.4)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-1500-595-CL-BK	B-595	Vinyl	BK on CL	1.500 (38.1)	25 ft. (7.6 m)	1 roll (cont.)
Fig. 33	XC-500-595-OR-BK	B-595	Vinyl	BK on OR	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-OR-BK	B-595	Vinyl	BK on OR	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-OR-BK	B-595	Vinyl	BK on OR	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-OR-BK	B-595	Vinyl	BK on OR	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-WT-BK	B-595	Vinyl	BK on WT	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-WT-BK	B-595	Vinyl	BK on WT	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-WT-BK	B-595	Vinyl	BK on WT	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-WT-BK	B-595	Vinyl	BK on WT	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-YL-BK	B-595	Vinyl	BK on YL	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-YL-BK	B-595	Vinyl	BK on YL	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-YL-BK	B-595	Vinyl	BK on YL	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-YL-BK	B-595	Vinyl	BK on YL	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-WT-RD	B-595	Vinyl	RD on WT	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-WT-RD	B-595	Vinyl	RD on WT	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-WT-RD	B-595	Vinyl	RD on WT	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-WT-RD	B-595	Vinyl	RD on WT	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-BL-WT	B-595	Vinyl	WT on BL	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-BL-WT	B-595	Vinyl	WT on BL	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-BL-WT	B-595	Vinyl	WT on BL	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-BL-WT	B-595	Vinyl	WT on BL	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-GN-WT	B-595	Vinyl	WT on GN	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-GN-WT	B-595	Vinyl	WT on GN	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-GN-WT	B-595	Vinyl	WT on GN	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-GN-WT	B-595	Vinyl	WT on GN	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-500-595-RD-WT	B-595	Vinyl	WT on RD	0.500 (12.7)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-750-595-RD-WT	B-595	Vinyl	WT on RD	0.750 (19.1)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1000-595-RD-WT	B-595	Vinyl	WT on RD	1.000 (25.4)	30 ft. (9.1 m)	1 roll (cont.)
Fig. 33	XC-1500-595-RD-WT	B-595	Vinyl	WT on RD	1.500 (38.1)	30 ft. (9.1 m)	1 roll (cont.)

PermaSleeve® PS Polyolefin Wire Marking Sleeves (B-342)

3:1 heat shrinkable sleeve fits snugly around wire for identification and protection. Fade resistant and flame retardant. Meets the following material and physical property specifications.

- SAE-AMS-DTL-23053/5 (Class 1)
- SAE-AS-81531
- MIL-STD-202
- RoHS Compliant
- UL Recognized
- Tested per: ASTM E162 and ASTM E662




Figure 44




Figure 58



Diagram	Part Number	B#	Color	Approx. Wire Gauge*	Range of Wire Dia. Inch (mm) Min. Max.	Sleeve Width A Inch (mm)	Supplied Diameter B Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeves per Roll
B-342 PermaSleeve® PS Polyolefin Wire Marking Sleeves										
Fig. 44	XPS-125-1	B-342	BK on WT	22 to 16	0.046 (1.2) - 0.110 (2.8)	1.015 (25.8)	0.125 (3.2)	0.047 (1.2)	.020 (0.5) ± .003 (0.07)	100
Fig. 58	XPS-125-CONT	B-342	BK on WT	22 to 16	0.046 (1.2) - 0.110 (2.8)	8 ft (2.45m)	0.125 (3.2)	0.047 (1.2)	.020 (0.5) ± .003 (0.07)	1 roll (cont.)
Fig. 58	XPS-125-CONT-YL-BK	B-342	BK on YL	22 to 16	0.046 (1.2) - 0.110 (2.8)	8 ft (2.45m)	0.125 (3.2)	0.047 (1.2)	.020 (0.5) ± .003 (0.07)	1 roll (cont.)
Fig. 44	XPS-187-1	B-342	BK on WT	20 to 10	0.062 (1.6) - 0.150 (3.8)	1.015 (25.8)	0.187 (4.7)	0.062 (1.6)	.020 (0.5) ± .003 (0.07)	100
Fig. 58	XPS-187-CONT	B-342	BK on WT	20 to 10	0.062 (1.6) - 0.150 (3.8)	8 ft (2.45m)	0.187 (4.7)	0.062 (1.6)	.020 (0.5) ± .003 (0.07)	1 roll (cont.)
Fig. 58	XPS-187-CONT-YL-BK	B-342	BK on YL	20 to 10	0.062 (1.6) - 0.150 (3.8)	8 ft (2.45m)	0.187 (4.7)	0.062 (1.6)	.020 (0.5) ± .003 (0.07)	1 roll (cont.)
Fig. 44	XPS-250-1	B-342	BK on WT	16 to 8	0.094 (2.4) - 0.215 (5.5)	1.015 (25.8)	0.250 (6.4)	0.093 (2.4)	.025 (0.6) ± .003 (0.07)	100
Fig. 58	XPS-250-CONT	B-342	BK on WT	16 to 8	0.094 (2.4) - 0.215 (5.5)	8 ft (2.45m)	0.250 (6.4)	0.093 (2.4)	.025 (0.6) ± .003 (0.07)	1 roll (cont.)
Fig. 58	XPS-250-CONT-YL-BK	B-342	BK on YL	16 to 8	0.094 (2.4) - 0.215 (5.5)	8 ft (2.45m)	0.250 (6.4)	0.093 (2.4)	.025 (0.6) ± .003 (0.07)	1 roll (cont.)
Fig. 44	XPS-375-1	B-342	BK on WT	12 to 4	0.125 (3.2) - 0.320 (8.13)	1.015 (25.8)	0.375 (9.5)	0.125 (3.1)	.025 (0.6) ± .003 (0.07)	100
Fig. 58	XPS-375-CONT	B-342	BK on WT	12 to 4	0.125 (3.2) - 0.320 (8.13)	8 ft (2.45m)	0.375 (9.5)	0.125 (3.1)	.025 (0.6) ± .003 (0.07)	1 roll (cont.)