



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
		G		REV PER ECR 10-000722	22JAN10	JR

D

C

B

A



AMP WIRE RANGE	Listed FILE E13288
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
2/0 AWG SOLID OR STRANDED	MS 20659-119 CLASS 2

- 1 STAMP AMP 2/OW* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 TIN PLATE 0/00254 [0.000100] MIN EXT THK PER ASTM B-545

321870

B

A

50	LOOSE PIECE	321870
QTY	PACKAGE TYPE	PART NO.
Tyco Electronics Corporation Harrisburg, PA 17105-3608		
NAME TERMINAL, RING TONGUE, SOLISTRAND		
SIZE	CAGE CODE	DRAWING NO
A2	00779	C=321870
RESTRICTED TO	—	
SCALE	SHEET	REV
2:1	1 of 1	G

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 1/14/94
VOLTAGE RATING: N/A	DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK AJ KAUFMAN 1/19/94
CIRCULAR MIL AREA: 60.6-76.3mm² [119,500-150,500] SOLID OR STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APVD JL MECKLEY 1/19/94
	MATERIAL - 2		PRODUCT SPEC —
			APPLICATION SPEC —
			WEIGHT —
			CUSTOMER DRAWING