

main menu



home

test & measurement

products

skills

download

online catalogue T&M

clamp-type test probes

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

- ▶ 2 mm system
- ▶ 2 mm safety system
- ▶ 4 mm system
- ▶ 4 mm sliding sleeve system
- ▶ 4 mm safety system

sockets

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions

Home ▶ plugs ▶ plugs ▶ VON 30

VON 30

 datasheet for VON 30
 article number: 930047104


View Full-Size Image



 SKS Kontakttechnik GmbH

search online catalogue

Search

Search

Messetermine

No events

QR-Code



product description:	order number: 930 047-104
description:	Fully mating connector, shatter-proof, flexible insulated sleeve. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 2.5 mm². Nickel-plated brass contact material.
typ:	VON 30 gruen/green
system:	4 mm system
order number:	930 047-104
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	4 mm
type of contact:	pin (spring loaded)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	30 A
Please consider derating curve!	
contact resistance:	3 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +70 °C
drawing	

