

STOR.E ALU 2

**STORE YOUR DATA
WITH A SOLID AND
STYLISH HARD DRIVE**



CHOOSE THE RIGHT SIZE

2.5" (6.4 cm) from 320 GB up to 1 TB capacity. And 3.5" (8.9 cm) from 500 GB up to 2 TB capacity.

PERFECT BODY

Stylish and solid aluminium casing for more safety.

A SIMPLE SOLUTION

Easy connectivity and installation for your needs.

WWW.TOSHIBA-MULTIMEDIA.COM



DRIVE



CASING



HIGH SPEED



2.5": NO POWER

TOSHIBA
Leading Innovation >>>

MAIN FEATURES

- High speed USB 2.0
- Solid aluminium casing
- Low power consumption
- Silent operation

**BASIC SPECIFICATION**

Formatted capacity:	2.5" (6.4 cm): 320 GB, 500 GB, 640 GB, 750 GB, 1 TB 3.5" (8.9 cm): 500 GB, 640 GB, 1 TB, 1.5 TB, 2 TB
Form factor:	2.5" (6.4 cm)/3.5" (8.9 cm)
USB interface:	High Speed USB 2.0
Interface transfer rate:	Up to 480 Mbps
Data buffer:	2 MB (@ < 250 GB), 8 MB (@ > 250 GB)
Power supply:	2.5" (6.4 cm): USB power/data connection 3.5" (8.9 cm): 24 W 12V/2A
On-bus power:	Up to 5 W
Dimensions (mm):	2.5" (6.4 cm): 120 (H) x 11.7 (W) x 77 (L) mm (<640 GB), 120 (H) x 14.5 (W) x 77 (L) mm (>750 GB) 3.5" (8.9 cm): 116 (H) x 34.5 (W) x 208.5 (L)
Weight (g):	2.5" (6.4 cm): 175 g, 197 g (750 GB/1 TB) 3.5" (8.9 cm): 1170 g
System requirements:	Microsoft® Windows®, XP/Vista/Windows 7, 1 x USB port
Box content:	2.5" (6.4 cm) STOR.E ALU 2: USB cable, Quick Start Guide, User's Manual (pre-installed on the hard drive), warranty leaflet, 3.5" (8.9 cm) STOR.E ALU 2: AC adaptor, power cable, USB cable, Quick Start Guide, User's Manual (pre-installed on the hard drive), warranty leaflet
Certifications:	CE, NCRS, SASO, GOST (3.5"), RoHS

COLOURS

3.5" (8.9 cm): silver



3.5" (8.9 cm): brown

2.5" (6.4 cm): silver
up to 640 GB2.5" (6.4 cm): brown
up to 640 GB2.5" (6.4 cm): black
750 GB/1 TB

Copyright © 2010 TOSHIBA Corporation. All Rights Reserved. Product specifications, configurations, prices and component / options availability are all subject to change without notice. Product design, specifications and colours are subject to change without notice and may vary from those shown. Error and omissions excepted.